

Surface mounting Mini Pragma (offer C)

1 row, 4 to 18 modules

2 and 3 rows, 12 modules per row

Function

Mini Pragma is a distribution or subdistribution enclosure up to 63 A. It is used indoors, in housing or the service sector, for new installations or renovation work.

Description

Technical data

- Equipped with an opaque or transparent, curved door:
 - 1 row: wicket door opens 90° upwards
 - 2 and 3 rows: door opens 180° to the right and to the left.
- Rated current of the enclosure:
 - 4 modules: 50 A
 - 6 to 36 modules: 63 A.
- Material:
 - colour: white RAL 9003.
- Compliance with standards:
 - complies with IEC 439.3 (EN 60-439-3).
- Degree of protection:
 - as in IEC 529: IP40 (protection against solids and liquids)
 - as in EN 50-102: IK07 (protection against mechanical impacts)
 - class 2 protection against indirect contact (with insulating plugs on the fixing screws).
- Fire and excessive heat withstand capacity as in IEC 695-2-1:
 - front panel and back: 750°C/5 s
 - N - earth terminal bar supports: 960°C/30 s
 - complies with BOP regulations in France (buildings open to the public).

Composition

Surface mounting Mini Pragma is composed of:

- a back with:
 - a centred oblong opening to simplify installation
 - oblong fixing holes enabling the adjustment of verticality
 - cable insertion kit:
 - punch-outs, on 4 panels for the 1 row enclosures
 - a large surface for punching (crown saw, punches) at the top and bottom of the 2 and 3 row enclosures
 - 1 to 3 metallic rails, screwed symmetrically onto the back
- a cover:
 - reversible front panel, equipped with blanking plates which can be punched-out
 - curved wicket door or curved door.

Accessories delivered with the enclosure

Surface mounting Mini Pragma is delivered equipped with:

- insulating plugs: to be placed on the back fixing screws to obtain a class 2 insulation
- a circuit identification strip per row: to be glued onto the front panel
- a connection assembly:
 - 1 terminal block
 - 1 terminal block support
- terminal block details:

Number of holes	Composition	
	10 [□]	16 [□]
4	2	2
8	4	4
16	8	8
20	10	10
32	16	16



Connection assembly



13324



13542

Surface mounting Mini Pragma (offer C)

1 row, 4 to 18 modules

2 and 3 rows, 12 modules per row (cont.)

Catalogue numbers

Enclosure with door					
Number of rows	Capacity in modules		Terminal blocks delivered (no. x no. holes)	Cat. no.	
	9 mm	18 mm		Opaque	Transparent
1	8	4	1 x 4	13321	13326
1	12	6	1 x 4	13322	13327
1	16	8	1 x 8	13323	13328
1	24	12	1 x 8	13324	13329
2	48	24	1 x 16	13532	13542
3	72	36	1 x 20	13533	13543

Additional information

Optional accessories: page 93010

Dimensions: page 93900