

Kaedra

Interfaces enclosures

Offer: T 750°C - 1 or 2 terminal blocks

Enclosures that can be installed alone, but also as an extension of another enclosure.



Kaedra interface enclosure.

Description

- This enclosure can also act as a cable duct.
- In enclosures with 3 or 4 openings, the kit for INS40/63/80 A must be mounted in the central openings.

Technical data

Kaedra switchboards guarantee a high degree of protection and increased dependability.

Enclosures		
In conformity with standards	Empty enclosures	IEC 60670-1 and 24
	Equipped switchboards	IEC 61439-1 and 3
Colour	Light grey RAL 7035 and transparent green door	
Degree of protection	IP	IP65 (as per IEC 60529)
	IK	IK09 (as per IEC 62262)
Insulating	Class 2	

Additional characteristics

Operating temperature	-25°C to +60°C
Flame and abnormal heat resistance	750°C, conform to regulations for establishments open to the general public and very high buildings
Resistance to chemicals and atmospheric agents, UVs	
Optional locking of the door, sealing of the front face and front plates	

Enclosure catalogue numbers

Technical data						Accessories delivered with an enclosure cat. no. ⁽²⁾		Cat. no		
Nb of op.	Dimensions (mm)			Pre-cutout (top and bottom) ⁽¹⁾			Plates for: buttons, indicator lights	65 x 85 mm outlets		
	W	H	D	M	20	25				32
				PG	11	16	21	13138	13136	
3	138	460	160		1	1	1	3	1	13973
4	138	610	160		1	1	1	4	1	13974

⁽¹⁾ Concentric pre-cutouts of the PG and ISO/metric type (EN 50262).

⁽²⁾ Accessories also delivered: class II plugs.