




























Range of weatherproof mini enclosures

1 row					
Offer A	13975	13976	13977	13978	13979
Offer B	13956	13957	13958	13959	13960
Offer C	10311	10312	10313	10314	10315
Offer D	-	13441	13442	13443	13444
Nbr of modules	3	4	6	8	12
Width	80	123	159	195	267
Height	150	200	200	200	200

Range of weatherproof enclosures

mm	138	236	340	448						
	5 modules	8 modules	12 modules per row	12 + 1 modules	18 modules per row (12 modules if interface)	18 + 1 modules				
280			 A : 13981 B : 13962 C : 10340 D : 13431		 A : 13982 B : 13963 C : 10341 D : 13432	 A : 13990 B : 13970 C : 10350 D : 13438				
335				 A : 13191 B : 13166 C : 10376						
460	 A : 13993 B : 13973 C : 10353	 A : 13189 B : 13164 C : 10374	 A : 13190 B : 13165 C : 10375	 A : 13983 B : 13964 C : 10342 D : 13433	 A : 13195 B : 13170 C : 10380	 A : 13192 B : 13167 C : 10377	 A : 13984 B : 13965 C : 10343 D : 13434	 A : 13991 B : 13971 C : 10351 D : 13439	 A : 13197 B : 13172 C : 10382	 A : 13193 B : 13168 C : 10378
610	 A : 13994 B : 13974 C : 10354		 A : 13985 B : 13966 C : 10344 D : 13435	 A : 13196 B : 13171 C : 10381	 A : 13986 B : 13967 C : 10345 D : 13436	 A : 13992 B : 13972 C : 10352 D : 13440	 A : 13198 B : 13173 C : 10383			
842					 A : 13987 B : 13968 C : 10346 D : 13437	 A : 13199 B : 13174 C : 10384				