

# Kaedra

## Versatile enclosures

Offer: T 650°C - without terminal block

The opaque door versatile enclosure provides a zone to install non-modular switchgear.

The versatile enclosure for power outlets provides a row for modular switchgear and a universal zone.



Versatile Kaedra enclosure.

### Description

#### Opaque door versatile enclosure

- Delivered with a slotted mounting plate mounted at the back
- Available depth for installation of non-modular switchgear on mounting plate: 130 mm
- Reversible front face to change door opening direction.

### Technical data

Kaedra switchboards guarantee a high degree of protection and increased dependability.

#### Enclosures

In conformity with standards	Empty enclosures	IEC 60670-1 and 24
	Equipped switchboards	IEC 61439-1 and 3
Colour	Light grey RAL 7035	
Degree of protection	IP	IP65 (as per IEC 60529)
	IK	IK09 (as per IEC 62262)
Insulating	Class 2	

#### Additional characteristics

Operating temperature	-25°C to +60°C
Flame and abnormal heat resistance	650°C as per IEC 60695-2-11
Resistance to chemicals and atmospheric agents, UVs	
Optional locking of the door, sealing of the front face and front plates	

Note: versatile enclosures for power outlets can accommodate power outlets up to 125 A.

### Enclosure catalogue numbers

Opaque door versatile enclosures			Cat. no. <sup>(1)</sup>	
Dimensions (mm)			Number of modules	
W	H	D		
340	460	160	5	10380
	610	160		10381
448	460	160	8	10382
	610	160		10383
	842	160		10384

(1) Accessories also delivered: class II plugs, mounting plate.

Versatile enclosures for power outlets			Cat. no. <sup>(1)</sup>	
Dimensions (mm)			Number of modules	
W	H	D		
138	460	160	5	10374
236	460	160	8	10375
340	335	160	12 + 1	10376
	460	160	12 + 1	10377
448	460	160	18 + 1	10378

(1) Accessories also delivered: class II plugs, blanking plates (5 modules of 18 mm) and marking kit.