







Boîtes à gradins IP55 - IK07

Couvercle		Enclipsable						Vis 1/4 de tour					
													
Dimensions (mm)	Int.	H	Ø	65	80	105	105	150	175	225	275	325	
		L	60	65	80	65	105	105	150	175	225	275	
		P	40	45	45	55	55	80	80	100	120	120	
	Ext.	H	Ø	74	89	116	116	164	193	241	291	341	
		L	69	74	89	74	116	121	164	194	241	291	
		P	69	54	51	62	62	87	87	107	128	128	
Nombre de gradins (Ø min. - max.)	4/20	4	4	7	7	8	-	-	-	-	-		
	4/25	-	-	-	-	-	7	10	10	4	-		
	4/32	-	-	-	-	-	-	-	2	8	16		
	4/40	-	-	-	-	-	-	-	-	4	10		
Standard	Gris 650°C	ENN05001	ENN05002	ENN05032	ENN05004	ENN05003	ENN05005	ENN05007	ENN05010	ENN05013	ENN05017	ENN05019	
	Blanc 650°C	ENN05021	ENN05022	ENN05072	ENN05024	ENN05023	ENN05025	-	-	-	-	-	
Équipées de borniers	Gris 650°C	-	-	-	ENN05204	-	ENN05205	-	-	-	-	-	
Pour circuits de sécurité	Rouge 960°C	-	-	-	ENN05164	-	ENN05165	ENN05167	-	-	-	-	
	Gris 960°C	-	-	-	ENN05264	-	ENN05265	ENN05267	-	-	-	-	

Boîtes avec entrées défonçables IP55 - IK07

Couvercle		Enclipsable						Vis 1/4 de tour					
													
Dimensions (mm)	Int.	H	Ø	65	80	105	105	150	175	225	275	325	
		L	60	65	80	65	105	105	150	175	225	275	
		P	40	45	45	55	55	80	80	100	120	120	
	Ext.	H	Ø	74	89	116	116	164	193	241	291	341	
		L	69	74	89	74	116	121	164	194	241	291	
		P	69	54	51	62	62	87	87	107	128	128	
Nombre d'entrées défonçables (Ø min. - max.)	12/16	-	-	-	-	-	8	8	-	-	-		
	16/20	-	4	4	6	7	4	-	-	-			
	20/25	-	-	-	-	-	2	4	6	16	24		
	25/32	-	-	-	-	-	-	4	-	-			
	32/40	-	-	-	-	-	-	-	6	8	8		
Standard	Gris 650°C	-	ENN05082	ENN05084	ENN05083	ENN05085	ENN05087	ENN05090	ENN05093	ENN05097	ENN05099		
	750°C	-	-	-	-	ENN05085	ENN05087	ENN05090	ENN05093	ENN05097	ENN05099		
Pour circuits de sécurité	Rouge 960°C	-	-	ENN05174	-	ENN05175	ENN05177	-	-	-	-		

Boîtes à faces lisses IP55 - IK07

Couvercle		Enclipsable						Vis 1/4 de tour					
													
Dimensions (mm)	Int.	H	Ø	65	80	105	105	150	175	225	275	325	
		L	60	65	80	65	105	105	150	175	225	275	
		P	40	45	45	55	55	80	80	100	120	120	
	Ext.	H	Ø	74	89	116	116	164	193	241	291	341	
		L	69	74	89	74	116	121	164	194	241	291	
		P	69	54	51	62	62	87	87	107	128	128	
Standard	Gris 650°C	-	-	ENN05044	-	-	ENN05047	ENN05050	ENN05053	ENN05057	ENN05059		
	Blanc 650°C	-	-	ENN05064	-	-	-	-	-	-			
	Gris 750°C	-	-	-	-	ENN05045	-	-	-	-			
	Blanc 750°C	-	-	-	-	ENN05065	-	-	-	-			