

# Product data sheet

## Characteristics

# AEH-LP02-G-5W

## LED Lamp – Mains Input



### Main

Power consumption by LED lamp	5 W
AC input voltage	90 - 270 V AC, 50 / 60 Hz
Maximum light output	460 Lumens
Efficiency of LED controller circuit	85%
Color of LEDs	White
Battery charging / Power ON (mains supply)	Green LED is ON
Cable to connect the lamp to mains	0.5 m, 20 AWG (0.5 mm <sup>2</sup> )
Low voltage disconnect	11.5 ± 0.1 V
<b>Product Certifications</b>	SONCAP

### Complementary Mechanical Specifications

Dimensions (L x B x H)	318 x 52 x 60 mm
Net weight	0.38 Kg
Gross weight	0.51 Kg

### Environment

Operating / Storage temperature	-10 to 55°C
Relative humidity	90%

### Packaging Information

Type	Dimensions (L x B x H in mm)	Net weight (Kg)	Gross weight (Kg)	No. of units
Unitary package	350 x 82 x 64	0.38	0.51	1
Group package	440 x 370 x 155	5.15	6	10
Pallet package	1200 x 1000 x 1095	216	251	360

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.