

AENOR

AENOR Product Certificate Low Voltage Material



030/002441

AENOR certifies that the organization

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office	35, RUE JOSEPH MONIER 92506 RUEIL MALMAISON CEDEX (Francia)
supplies	Switches for household and similar fixed-electrical installations
in compliance with	UNE-EN 60669-1/A1:2003 (EN 60669-1:1999/A1:2002) UNE-EN 60669-1:2002 (EN 60669-1:1999) UNE-EN 60669-1:2002/A1:2003 CORR:2007 (EN 60669-1:1999/A1:2002 CORR:2007) UNE-EN 60669-1:2002/A2:2009 (EN 60669-1:1999/A2:2008)
References	Specified in Annex to the Certificate
Production site	UL. BUGNO, 1 78-400 SZCZECINEK (Polonia)
Certification scheme	In order to grant this Certificate, AENOR has tested the product and has verified the quality system implemented for its manufacture. AENOR performs these tasks periodically while the Certificate has not been cancelled, in accordance with Specific Rules RP 30.11.
First issued on	2017-01-23
Validity date	2022-01-23

Avelino BRITO
Chief Executive Officer

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com

Product certification body accredited by ENAC, number 01/C-PR275

AENOR

AENOR Product Certificate Low Voltage Material

030/002441

Annex to Certificate

Trade mark: Schneider Electric

Type Ref.	Pattern number	Rated current	Rated voltage	Type of product	Assembled with Ref.	IP Code	Additional information
E1111 + NHA56501 02.	1 momentary	10 A	250 V-	Main part	EAV92345 02, NHA37317 02, NHA37318 02	IP55	Screwless terminals
E1131 + NHA56501 02.	1 + 1 momentary	10 A	250 V-	Main part	EAV92346 02, NHA37320 02, NHA37321 02	IP55	Screwless terminals
E1151 + NHA56501 02.	5 momentary	10 A	250 V-	Main part	EAV92346 02, NHA37320 02, NHA37321 02	IP55	Screwless terminals
E1160 + NHA56501 02.	6	10 A	250 V-	Main part	EAV92345 02, NHA37317 02, NHA37318 02	IP55	Screwless terminals
E1170 + NHA56501 02.	7	10 AX	250 V-	Main part	EAV92345 02, NHA37317 02, NHA37318 02	IP55	Screwless terminals
E1190 + NHA56501 02.	6 + 6	10 AX	250 V-	Main part	EAV92346 02, NHA37320 02, NHA37321 02	IP55	Screwless terminals
E1320 + NHA56501 02.	2	16 AX	250 V-	Main part	NHA37316 02	IP55	Screwless terminals

First issued on 2017-01-23
Validity date 2022-01-23

Original Electrónico

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com

Product certification body accredited by ENAC, number 01/C-PR275

AENOR

Additional Certificate information

030/002441

Assembled references:

Reference	Main part	Rocker	Pilot light	Surface mounting box	Flush mounting supporting frame	Additional information
MUR35626	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR35026	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR35027	E1111 + NHA56501 02	EAV92345 02	---	---	---	1 elem. Grey
MUR39026	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR39027	E1111 + NHA56501 02	EAV92345 02	---	---	---	1 elem. White
MUR39626	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR40009	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR40019	E1111 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR35127	E1111 + NHA56501 02	NHA37317 02	S520292	---	---	1 elem. Grey
MUR36628	E1111 + NHA56501 02	NHA37317 02	S520292	---	EAV92354 02	1 elem. Grey
MUR39127	E1111 + NHA56501 02	NHA37317 02	S520292	---	---	1 elem. White
MUR40010	E1111 + NHA56501 02	NHA37317 02	S520292	EAV92338 02	---	1 elem. White
MUR35028	E1111 + NHA56501 02	NHA37317 02	S520292	EAV92338 02	---	1 elem. Grey
MUR35628	E1111 + NHA56501 02	NHA37317 02	S520292	EAV92338 02	---	1 elem. Grey
MUR40002	E1111 + NHA56501 02	NHA37317 02	S520292	---	EAV92354 02	1 elem. Grey
MUR39628	E1111 + NHA56501 02	NHA37317 02	S520292	EAV92338 02	---	1 elem. White
MUR39629	E1111 + NHA56501 02	NHA37317 02	S520292	---	EAV92354 02	1 elem. White
MUR40020	E1111 + NHA56501 02	NHA37317 02	S520292	EAV92338 02	---	1 elem. Grey
MUR40021	E1111 + NHA56501 02	NHA37317 02	S520292	---	EAV92354 02	1 elem. White
MUR34029	E1111 + NHA56501 02	NHA37318 02	---	---	---	1 elem. Grey
MUR39129	E1111 + NHA56501 02	NHA37318 02	---	---	---	1 elem. White
MUR35326	E1131 + NHA56501 02	NHA37320 02 + NHA37321 02	---	---	---	1 elem. Grey
MUR35228	E1131 + NHA56501 02	NHA37320 02 + NHA37321 02	S520291 x2	---	---	1 elem. Grey
MUR35042	E1151 + NHA56501 02	EAV92346 02 x2	---	---	---	1 elem. Grey
MUR36624	E1160 + NHA56501 02	NHA37317 02	S520291	---	EAV92354 02	1 elem. Grey
MUR35024	E1160 + NHA56501 02	NHA37317 02	S520291	EAV92338 02	---	1 elem. Grey
MUR35025	E1160 + NHA56501 02	NHA37317 02	S520291	---	---	1 elem. Grey
MUR35624	E1160 + NHA56501 02	NHA37317 02	S520291	EAV92338 02	---	1 elem. Grey
MUR39024	E1160 + NHA56501 02	NHA37317 02	S520291	---	---	1 elem. White
MUR35021	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR35621	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR37021	E1160 + NHA56501 02	EAV92345 02	---	---	---	1 elem. Grey
MUR39021	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR39721	E1160 + NHA56501 02	EAV92345 02	---	---	EAV92354 02	1 elem. White, with Claws
MUR39723	E1160 + NHA56501 02	EAV92345 02	---	---	---	1 elem. White
MUR40000	E1160 + NHA56501 02	EAV92345 02	---	---	EAV92354 02	1 elem. White
MUR40013	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR40015	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR39621	E1160 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. White
MUR36024	E1160 + NHA56501 02	EAV92345 02	---	EAV92356 02	---	2 elem. Grey with socket outlet: EAV92343 02 screwless + EAV92336 02
MUR39623	E1160 + NHA56501 02	NHA37317 02	S520291	---	EAV92354 02	1 elem. White
MUR39624	E1160 + NHA56501 02	NHA37317 02	S520291	EAV92338 02	---	1 elem. White
MUR40004	E1160 + NHA56501 02	NHA37317 02	S520291	EAV92338 02	---	1 elem. Grey

AENOR

Additional Certificate information

030/002441

MUR40017	E1160 + NHA56501 02	NHA37317 02	S520291	---	EAV92354 02	1 elem. White
MUR40018	E1160 + NHA56501 02	NHA37317 02	S520291	EAV92338 02	---	1 elem. White
MUR35020	E1170 + NHA56501 02	EAV92345 02	---	---	---	1 elem. Grey
MUR35023	E1170 + NHA56501 02	EAV92345 02	---	EAV92338 02	---	1 elem. Grey
MUR39023	E1170 + NHA56501 02	EAV92345 02	---	---	---	1 elem. White
MUR39622	E1190 + NHA56501 02	EAV92346 02 x2	---	EAV92338 02	---	1 elem. White
MUR35019	E1190 + NHA56501 02	EAV92346 02 x2	---	---	---	1 elem. Grey
MUR35022	E1190 + NHA56501 02	EAV92346 02 x2	---	EAV92338 02	---	1 elem. Grey
MUR35622	E1190 + NHA56501 02	EAV92346 02 x2	---	EAV92338 02	---	1 elem. Grey
MUR39022	E1190 + NHA56501 02	EAV92346 02 x2	---	---	---	1 elem. White
MUR40001	E1190 + NHA56501 02	EAV92346 02 x2	---	---	EAV92354 02	1 elem. White
MUR40014	E1190 + NHA56501 02	EAV92346 02 x2	---	EAV92338 02	---	1 elem. Grey
MUR40016	E1190 + NHA56501 02	EAV92346 02 x2	---	EAV92338 02	---	1 elem. White
MUR35033	E1320 + NHA56501 02	NHA37316 02	---	EAV92338 02	---	1 elem. Grey
MUR35034	E1320 + NHA56501 02	NHA37316 02	---	---	---	1 elem. Grey
MUR39033	E1320 + NHA56501 02	NHA37316 02	---	---	---	1 elem. White
MUR40007	E1320 + NHA56501 02	NHA37316 02	---	EAV92338 02	---	1 elem. White
MUR40008	E1320 + NHA56501 02	NHA37316 02	---	EAV92338 02	---	1 elem. Grey
MUR34201	---	EAV92345 02	---	---	---	1 elem. Grey
MUR39201	---	EAV92345 02	---	---	---	1 elem. White
MUR34202	---	EAV92345 02	---	---	---	1 elem. Grey
MUR39202	---	EAV92345 02	---	---	---	1 elem. White
MUR34204	---	NHA37317 02	---	---	---	1 elem. Grey
MUR39204	---	NHA37317 02	---	---	---	1 elem. White
MUR34203	---	NHA37318 02	---	---	---	1 elem. Grey
MUR39203	---	NHA37318 02	---	---	---	1 elem. White
MUR34205	---	NHA37320 02 + NHA37321 02	---	---	---	1 elem. Grey
MUR39205	---	NHA37320 02 + NHA37321 02	---	---	---	1 elem. White
S520291	---	---	S520291	---	---	---
S520292	---	---	S520292	---	---	---

Pilot light

Type reference	Rated current	Rated Voltage	Type of product	To be mounted with ref.	Additional information
S520291	0,15 mA	250 V~	Pilot light	All references	With wires connection
S520292	0,15 mA	250 V~	Pilot light	E1111 / E1111	With plugs connection