

**- List of certificate of conformity ASEFA -**

Update of 21-04-2017

Certif_ASEFA	Ref_commercial	Version	Designation	PD	Ur	Isc	Ir
12-42-327-02	EXE172512A1B	fixed version	EasyPact EXE 17,5kV 25kA 1250A (145mm)	145	17	25	12
11-42-327-02	EXE172508A1B	fixed version	EasyPact EXE 17,5kV 25kA 800A (145mm)	145	17	25	08
10-42-327-02	EXE172506A1B	fixed version	EasyPact EXE 17,5kV 25kA 630A (145mm)	145	17	25	06
09-42-327-02	EXE172012A1B	fixed version	EasyPact EXE 17,5kV 20kA 1250A (145mm)	145	17	20	12
08-42-327-02	EXE172008A1B	fixed version	EasyPact EXE 17,5kV 20kA 800A (145mm)	145	17	20	08
07-42-327-02	EXE172006A1B	fixed version	EasyPact EXE 17,5kV 20kA 630A (145mm)	145	17	20	06
06-42-327-02	EXE122512A1B	fixed version	EasyPact EXE 12kV 25kA 1250A (145mm)	145	12	25	12
05-42-327-02	EXE122508A1B	fixed version	EasyPact EXE 12kV 25kA 800A (145mm)	145	12	25	08
04-42-327-02	EXE122506A1B	fixed version	EasyPact EXE 12kV 25kA 630A (145mm)	145	12	25	06
03-42-327-02	EXE122012A1B	fixed version	EasyPact EXE 12kV 20kA 1250A (145mm)	145	12	20	12
02-42-327-02	EXE122008A1B	fixed version	EasyPact EXE 12kV 20kA 800A (145mm)	145	12	20	08
01-42-327-02	EXE122006A1B	fixed version	EasyPact EXE 12kV 20kA 630A (145mm)	145	12	20	06
30-42-327-02	EXE172512K1B	fixed version	EasyPact EXE 17,5kV 25kA 1250A (150mm)	150	17	25	12
29-42-327-02	EXE172508K1B	fixed version	EasyPact EXE 17,5kV 25kA 800A (150mm)	150	17	25	08
28-42-327-02	EXE172506K1B	fixed version	EasyPact EXE 17,5kV 25kA 630A (150mm)	150	17	25	06
27-42-327-02	EXE172012K1B	fixed version	EasyPact EXE 17,5kV 20kA 1250A (150mm )	150	17	20	12
26-42-327-02	EXE172008K1B	fixed version	EasyPact EXE 17,5kV 20kA 800A (150mm)	150	17	20	08
25-42-327-02	EXE172006K1B	fixed version	EasyPact EXE 17,5kV 20kA 630A (150mm)	150	17	20	06
24-42-327-02	EXE122512K1B	fixed version	EasyPact EXE 12kV 25kA 1250A (150mm)	150	12	25	12
23-42-327-02	EXE122508K1B	fixed version	EasyPact EXE 12kV 25kA 800A (150mm)	150	12	25	08
22-42-327-02	EXE122506K1B	fixed version	EasyPact EXE 12kV 25kA 630A (150mm)	150	12	25	06
21-42-327-02	EXE122012K1B	fixed version	EasyPact EXE 12kV 20kA 1250A (150mm)	150	12	20	12
20-42-327-02	EXE122008K1B	fixed version	EasyPact EXE 12kV 20kA 800A (150mm)	150	12	20	08
19-42-327-02	EXE122006K1B	fixed version	EasyPact EXE 12kV 20kA 630A (150mm)	150	12	20	06
48-42-327-02	EXE172512B1B	fixed version	EasyPact EXE 17,5kV 25kA 1250A (185mm)	185	17	25	12
47-42-327-02	EXE172508B1B	fixed version	EasyPact EXE 17,5kV 25kA 800A (185mm)	185	17	25	08
46-42-327-02	EXE172506B1B	fixed version	EasyPact EXE 17,5kV 25kA 630A (185mm)	185	17	25	06
45-42-327-02	EXE172012B1B	fixed version	EasyPact EXE 17,5kV 20kA 1250A (185mm)	185	17	20	12
44-42-327-02	EXE172008B1B	fixed version	EasyPact EXE 17,5kV 20kA 800A (185mm)	185	17	20	08
43-42-327-02	EXE172006B1B	fixed version	EasyPact EXE 17,5kV 20kA 630A (185mm)	185	17	20	06
42-42-327-02	EXE122512B1B	fixed version	EasyPact EXE 12kV 25kA 1250A (185mm)	185	12	25	12
41-42-327-02	EXE122508B1B	fixed version	EasyPact EXE 12kV 25kA 800A (185mm)	185	12	25	08
40-42-327-02	EXE122506B1B	fixed version	EasyPact EXE 12kV 25kA 630A (185mm)	185	12	25	06
39-42-327-02	EXE122012B1B	fixed version	EasyPact EXE 12kV 20kA 1250A (185mm)	185	12	20	12
38-42-327-02	EXE122008B1B	fixed version	EasyPact EXE 12kV 20kA 800A (185mm)	185	12	20	08
37-42-327-02	EXE122006B1B	fixed version	EasyPact EXE 12kV 20kA 630A (185mm)	185	12	20	06
70-42-327-02	EXE172512L1B	fixed version	EasyPact EXE 17,5kV 25kA 1250A (210mm)	210	17	25	12
69-42-327-02	EXE172508L1B	fixed version	EasyPact EXE 17,5kV 25kA 800A (210mm)	210	17	25	08

**- List of certificate of conformity ASEFA -**

Update of 21-04-2017

Certif_ASEFA	Ref_commercial	Version	Designation	PD	Ur	Isc	Ir
68-42-327-02	EXE172506L1B	fixed version	EasyPact EXE 17,5kV 25kA 630A (210mm)	210	17	25	06
67-42-327-02	EXE172012L1B	fixed version	EasyPact EXE 17,5kV 20kA 1250A (210mm)	210	17	20	12
66-42-327-02	EXE172008L1B	fixed version	EasyPact EXE 17,5kV 20kA 800A (210mm)	210	17	20	08
65-42-327-02	EXE172006L1B	fixed version	EasyPact EXE 17,5kV 20kA 630A (210mm)	210	17	20	06
64-42-327-02	EXE122512L1B	fixed version	EasyPact EXE 12kV 25kA 1250A (210mm)	210	12	25	12
63-42-327-02	EXE122508L1B	fixed version	EasyPact EXE 12kV 25kA 800A (210mm)	210	12	25	08
62-42-327-02	EXE122506L1B	fixed version	EasyPact EXE 12kV 25kA 630A (210mm)	210	12	25	06
61-42-327-02	EXE122012L1B	fixed version	EasyPact EXE 12kV 20kA 1250A (210mm)	210	12	20	12
60-42-327-02	EXE122008L1B	fixed version	EasyPact EXE 12kV 20kA 800A (210mm)	210	12	20	08
59-42-327-02	EXE122006L1B	fixed version	EasyPact EXE 12kV 20kA 630A (210mm)	210	12	20	06
18-42-327-02	EXE173112A1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1250A (145mm)	145	17	31	12
17-42-327-02	EXE173108A1B	fixed version	EasyPact EXE 17,5kV 31,5kA 800A (145mm)	145	17	31	08
16-42-327-02	EXE173106A1B	fixed version	EasyPact EXE 17,5kV 31,5kA 630A (145mm)	145	17	31	06
15-42-327-02	EXE123112A1B	fixed version	EasyPact EXE 12kV 31,5kA 1250A (145mm)	145	12	31	12
14-42-327-02	EXE123108A1B	fixed version	EasyPact EXE 12kV 31,5kA 800A (145mm)	145	12	31	08
13-42-327-02	EXE123106A1B	fixed version	EasyPact EXE 12kV 31,5kA 630A (145mm)	145	12	31	06
36-42-327-02	EXE173112K1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1250A (150mm)	150	17	31	12
35-42-327-02	EXE173108K1B	fixed version	EasyPact EXE 17,5kV 31,5kA 800A (150mm)	150	17	31	08
34-42-327-02	EXE173106K1B	fixed version	EasyPact EXE 17,5kV 31,5kA 630A (150mm)	150	17	31	06
33-42-327-02	EXE123112K1B	fixed version	EasyPact EXE 12kV 31,5kA 1250A (150mm)	150	12	31	12
32-42-327-02	EXE123108K1B	fixed version	EasyPact EXE 12kV 31,5kA 800A (150mm)	150	12	31	08
31-42-327-02	EXE123106K1B	fixed version	EasyPact EXE 12kV 31,5kA 630A (150mm)	150	12	31	06
54-42-327-02	EXE173112B1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1250A (185mm)	185	17	31	12
53-42-327-02	EXE173108B1B	fixed version	EasyPact EXE 17,5kV 31,5kA 800A (185mm)	185	17	31	08
52-42-327-02	EXE173106B1B	fixed version	EasyPact EXE 17,5kV 31,5kA 630A (185mm)	185	17	31	06
51-42-327-02	EXE123112B1B	fixed version	EasyPact EXE 12kV 31,5kA 1250A (185mm)	185	12	31	12
50-42-327-02	EXE123108B1B	fixed version	EasyPact EXE 12kV 31,5kA 800A (185mm)	185	12	31	08
49-42-327-02	EXE123106B1B	fixed version	EasyPact EXE 12kV 31,5kA 630A (185mm)	185	12	31	06
76-42-327-02	EXE173112L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1250A (210mm )	210	17	31	12
75-42-327-02	EXE173108L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 800A (210mm)	210	17	31	08
74-42-327-02	EXE173106L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 630A (210mm)	210	17	31	06
73-42-327-02	EXE123112L1B	fixed version	EasyPact EXE 12kV 31,5kA 1250A (210mm)	210	12	31	12
72-42-327-02	EXE123108L1B	fixed version	EasyPact EXE 12kV 31,5kA 800A (210mm)	210	12	31	08
71-42-327-02	EXE123106L1B	fixed version	EasyPact EXE 12kV 31,5kA 630A (210mm)	210	12	31	06
58-42-327-02a	EXE173120B1B	fixed version	EasyPact EXE 17,5kV 31,5kA 2000A (185mm)	185	17	31	20
57-42-327-02a	EXE173116B1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1600A (185mm)	185	17	31	16
56-42-327-02a	EXE123120B1B	fixed version	EasyPact EXE 12kV 31,5kA 2000A (185mm)	185	12	31	20
55-42-327-02a	EXE123116B1B	fixed version	EasyPact EXE 12kV 31,5kA 1600A (185mm)	185	12	31	16

**- List of certificate of conformity ASEFA -**

Update of 21-04-2017

Certif_ASEFA	Ref_commercial	Version	Designation	PD	Ur	Isc	Ir
82-42-327-02a	EXE173125L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 2500A (210mm)	210	17	31	25
81-42-327-02a	EXE173120L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 2000A (210mm)	210	17	31	20
80-42-327-02a	EXE173116L1B	fixed version	EasyPact EXE 17,5kV 31,5kA 1600A (210mm)	210	17	31	16
79-42-327-02a	EXE123125L1B	fixed version	EasyPact EXE 12kV 31,5kA 2500A (210mm)	210	12	31	25
78-42-327-02a	EXE123120L1B	fixed version	EasyPact EXE 12kV 31,5kA 2000A (210mm)	210	12	31	20
77-42-327-02a	EXE123116L1B	fixed version	EasyPact EXE 12kV 31,5kA 1600A (210mm)	210	12	31	16
84-42-327-02a	EXE173125C1B	fixed version	EasyPact EXE 17,5kV 31,5kA 2500A (240mm)	240	17	31	25
83-42-327-02a	EXE123125C1B	fixed version	EasyPact EXE 12kV 31,5kA 2500A (240mm)	240	12	31	25
86-42-327-02a	EXE173125M1B	fixed version	EasyPact EXE 17,5kV 31,5kA 2500A (275mm)	275	17	31	25
85-42-327-02a	EXE123125M1B	fixed version	EasyPact EXE 12kV 31,5kA 2500A (275mm)	275	12	31	25
90-42-327-02a	EXE122506K1B	withdrawable version	EasyPact EXE 12kV 25kA 630A (150mm)	150	12	25	06
87-42-327-02a	EXE122006K1B	withdrawable version	EasyPact EXE 12kV 20kA 630A (150mm)	150	12	20	06
92-42-327-02a	EXE122512K1B	withdrawable version	EasyPact EXE 12kV 25kA 1250A (150mm)	150	12	25	12
91-42-327-02a	EXE122508K1B	withdrawable version	EasyPact EXE 12kV 25kA 800A (150mm)	150	12	25	08
89-42-327-02	EXE122012K1B	withdrawable version	EasyPact EXE 12kV 20kA 1250A (150mm)	150	12	20	12
88-42-327-02a	EXE122008K1B	withdrawable version	EasyPact EXE 12kV 20kA 800A (150mm)	150	12	20	08
99-42-327-02a	EXE122506L1B	withdrawable version	EasyPact EXE 12kV 25kA 630A (210mm)	210	12	25	06
96-42-327-02a	EXE122006L1B	withdrawable version	EasyPact EXE 12kV 20kA 630A (210mm)	210	12	20	06
101-42-327-02a	EXE122512L1B	withdrawable version	EasyPact EXE 12kV 25kA 1250A (210mm)	210	12	25	12
100-42-327-02a	EXE122508L1B	withdrawable version	EasyPact EXE 12kV 25kA 800A (210mm)	210	12	25	08
98-42-327-02a	EXE122012L1B	withdrawable version	EasyPact EXE 12kV 20kA 1250A (210mm)	210	12	20	12
97-42-327-02a	EXE122008L1B	withdrawable version	EasyPact EXE 12kV 20kA 800A (210mm )	210	12	20	08
93-42-327-02	EXE123106K1B	withdrawable version	EasyPact EXE 12kV 31,5kA 630A (150mm)	150	12	31	06
95-42-327-02	EXE123112K1B	withdrawable version	EasyPact EXE 12kV 31,5kA 1250A (150mm)	150	12	31	12
94-42-327-02	EXE123108K1B	withdrawable version	EasyPact EXE 12kV 31,5kA 800A (150mm)	150	12	31	08
102-42-327-02a	EXE123106L1B	withdrawable version	EasyPact EXE 12kV 31,5kA 630A (210mm)	210	12	31	06
104-42-327-02a	EXE123112L1B	withdrawable version	EasyPact EXE 12kV 31,5kA 1250A (210mm)	210	12	31	12
103-42-327-02a	EXE123108L1B	withdrawable version	EasyPact EXE 12kV 31,5kA 800A (210mm)	210	12	31	08
106-42-327-02a	EXE123120L1B	withdrawable version	EasyPact EXE 12kV 31,5kA 2000A (210mm)	210	12	31	20
105-42-327-02a	EXE123116L1B	withdrawable version	EasyPact EXE 12kV 31,5kA 1600A (210mm)	210	12	31	16