

LICENCE

No. 17332 - Issue No 2

Issued to:

Applicant:

Schneider Electric Industries SAS
35 Rue Joseph Monier
92506 RUEIL MALMAISON Cedex
France

Licensee:

Schneider Electric Industries SAS
35 Rue Joseph Monier
92506 RUEIL MALMAISON Cedex
France



Product : socket-outlets (2-pole)
Trade name(s) : MERTEN, SCHNEIDER ELECTRIC
Type(s)/model(s) : Series 270/... (see details in appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 382

SGS CEBEC hereby grants the right to use the CEBEC certification mark

The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 07/11/2016

ir. C. Lana,
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed

This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	socket-outlets (2-pole)
Trade name(s)	:	MERTEN, SCHNEIDER ELECTRIC
Type(s)/Model(s)	:	Series 270/... (see details in appendix)
rated voltage (Un)	:	250 Vac
rated current (In)	:	16 A
type of terminals	:	screw type
method of installation	:	claw or screw
method of mounting	:	flush type
degree of protection	:	IP 20 / IP 21 / IP 44
existence of shutters	:	with shutters
earthing	:	with earthing pin
markings	:	are shown on the body

Additional information

See Appendix

TESTS

Test requirements

NBN C 61-112-1 based on IEC 60884-1:2002 + A1:2006

Test results

The test results are laid down in certification file ref.591414/06

Remarks

This certificate is based on certificate ref. CB DE1-43044 and test reports ref. 5008062-1520-0005/129756 & 5008062-1520-0005/129756 part 2


Conclusion

The examination proved that all test requirements were met.

Checked by, project leader : Luigi Zanutto - 07/11/2016

Department Manager,
Product Certification :

Certification Manager :

A handwritten signature in blue ink, followed by the date '2016-11-07'.

FACTORY LOCATION(S)

Merten GmbH
Fritz-Kotz-Straße, 8
51674 WIEHL-BOMIG
Germany

Socket-outlet Series 270, screw type terminal

Center frame

Type No.	Description
System M	
2852	Shutter
2779-2779	Hinged lid + shutter
2779-4001	Hinged lid + shutter + IP44 sealing ring
2779-2474	Hinged lid + shutter + big labeling field
2534-2334	LED lighting module, light outlet
2534-2005	Labeling field, surge protection module
2534-2003	Labeling field, LED indicator lamp module
System Design	
2851	Shutter
2795-2878	Hinged lid + shutter
2795-4001	Hinged lid + shutter + IP44 sealing ring
2795-2478	Hinged lid + shutter + big labeling field

Cover frames

System Design (Thermo + Duro)		
	ARTEC	Antik
1 gang	4811	4831
2 gang	4812	4831
3 gang	4813	4831
4 gang	4814	4831
5 gang	4815	4831

System M (Thermo + Duro)		
	M-Plan	M-Plan for labeling
1 gang	4861	4861
2 gang	4862	4862 Vert & Hor
3 gang	4863	4863 Vert & Hor
4 gang	4864	
5 gang	4865	

System M (Thermo + Duro)		
	M-ARC	M-Star
1 gang	4851	4871
2 gang	4852	4872
3 gang	4853	4873
4 gang	4854	4874
5 gang	4855	4875

System M (Thermo + Duro)		
	M-Smart	M-Smart for labelling
1 gang	4841	4841
2 gang	4842	4842 Vert & Hor
3 gang	4843	4843 Vert & Hor
4 gang	4844	4844 Vert & Hor
5 gang	4845	4845 Vert & Hor

System M (Thermo + Duro)				
Elegance				
1 gang	4021	4031	4041	4051
2 gang	4022	4032	4042	4052
3 gang	4023	4033	4043	4053
4 gang	4024	4034	4044	4054
5 gang	4025	4035	4045	4055

Lighting accessories

Description	Catalogue No.
LED lighting module, light outlet	2334