



中国国家强制性产品认证证书

证书编号: 2014010304680069

委托人名称、地址

施耐德电气制造(武汉)有限公司
湖北省武汉市东湖开发区珞瑜路546号科技会展中心二期8楼807室

生产者(制造商)名称、地址

施耐德电气制造(武汉)有限公司
湖北省武汉市东湖开发区珞瑜路546号科技会展中心二期8楼807室

生产企业名称、地址

施耐德电气制造(武汉)有限公司
武汉市东湖新技术开发区佛祖岭三路一号

产品名称和系列、规格、型号

交流接触器

LC1D188...C, LC1D258...C, LC1DT32...C, LC2DT32...C, LC1DT40...C,
LC2DT40...C, 详见参数附件

产品标准和技术要求

GB 14048.4-2010

上述产品符合强制性产品认证实施规则
CNCA-01C-011:2007的要求, 特发此证。

发证日期: 2014年03月12日 有效期至: 2019年03月12日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 0896315



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2014010304680069

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
Room 807, 8F, Phase II Wuhan Science & Technology Conference & Exhibition
Center, No.546 Luoyu Road, Donghu Hi-Tech Development Zone, Wuhan, Hubei
Province, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
Room 807, 8F, Phase II Wuhan Science & Technology Conference & Exhibition
Center, No.546 Luoyu Road, Donghu Hi-Tech Development Zone, Wuhan, Hubei
Province, P.R.China

NAME AND ADDRESS OF THE FACTORY

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No 1, 3rd Road of Fo Zu Ling, Donghu New&High Tech Dev Zone Wu Han

NAME, MODEL AND SPECIFICATION

AC Contactor

LC1D188...C, LC1D258...C, LC1DT32...C, LC2DT32...C, LC1DT40...C,
LC2DT40...C; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4-2010

This is to certify that the above mentioned products have met the
requirements of implementation rules for compulsory certification(REF
NO. CNCA-01C-011:2007).

Date of issue: Mar.12,2014 Date of expiry: Mar.12,2019

Validity of this certificate is subject to positive result of the regular
follow up inspection by issuing certification body until the expiry date.

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE



Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

Q 0896315



中国国家强制性产品认证证书

附录:

第 1 页 共 4 页

证书编号: 2014010304680069

纸号: 896315

LC1D188...C, LC1D258...C, LC1DT32...C, LC2DT32...C, LC1DT40...C,
LC2DT40...C

LC1D188...C, LC1DT32...C, LC2DT32...C :

Ith:32A;

AC-3 : 220V/230V/380V/400V/18A , 660V/690V/11.5A ;

AC-4 : 220V/230V/380V/400V/15A , 660V/690V/9.6A ;

LC1D258...C, LC1DT40...C, LC2DT40...C:

Ith:40A ;

Ue/le:

AC-3:220V/230V/380V/400V/25A, 660V/690V/16.5A ;

AC-4:220V/230V/380V/400V/20.9A, 660V/690V/13.8A ;

Us:12V(AC50/60Hz) 、 21V(AC50/60Hz) 、 24V(AC50/60Hz) 、

32V(AC50/60Hz) 、 36V(AC50/60Hz) 、 42V(AC50/60Hz) 、

48V(AC50/60Hz) 、 60V(AC50/60Hz) 、 100V(AC50/60Hz) 、

110V(AC50/60Hz) 、 115V(AC50/60Hz)、 120V(AC50/60Hz)、

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 4 页

证书编号: 2014010304680069

纸号: 896315

127V(AC50/60Hz)、140V(AC50/60Hz)、200V(AC50/60Hz)、
208V(AC50/60Hz)、220V(AC50/60Hz)、230V(AC50/60Hz)、
240~230V(AC50Hz, AC50/60Hz)、277V(AC50/60Hz)、
380V(AC50/60Hz)、400V(AC50/60Hz)、415V(AC50/60Hz)、
440V(AC50/60Hz)、480V(AC50/60Hz)、480V(AC60Hz)、
500V(AC50/60Hz)、575V(AC50/60Hz)、575V(60Hz)、
600V(AC50/60Hz)、600V(AC60Hz)、660V(AC50/60Hz)、690V(AC50/60Hz)、
12V(DC)、20V(DC)、24V(DC)、32V(DC)、36V(DC)、
48V(DC)、60V(DC)、72V(DC)、96V(DC)、100V(DC)、
110V(DC)、125V(DC)、155V(DC)、174V(DC)、200V(DC)、
220V(DC)、250V(DC)、305V(DC)、348V(DC)、440V(DC);
4P;
配用辅助触头:
AC-15, Ue/le: 120V/6A, 600V/1.2A;
DC-13, Ue/le: 125V/1.1A, 600V/0.2A

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 3 页 共 4 页

证书编号: 2014010304680069

纸号: 896315

型号的解释:

LC1D	258	B7	C
I	II	III	IV

I	接触器基本型号 LC1D 交流接触器基本型号 LC2D 可逆交流接触器基本型号
II	规格: 188, 258, 2NO+2NC 132, 140, 4NO
III	线圈电压代码 见下表
IV	C, 中国制造

线圈电压代码

代码	电压	频率	代码	电压	频率
J7	12	50/60Hz	V7	400	50/60Hz
Z7	21	50/60Hz	N7	415	50/60Hz
B7	24	50/60Hz	R7	440	50/60Hz
C7	32	50/60Hz	T7	480	50/60Hz
CC7	36	50/60Hz	T6	480	60Hz
D7	42	50/60Hz	S7	500	50/60Hz
F7	48	50/60Hz	SC7	575	50/60Hz
EE7	60	50/60Hz	S6	575	60Hz
K7	100	50/60Hz	X7	600	50/60Hz
F7	110	50/60Hz	X6	600	60Hz
EE7	115	50/60Hz	YC7	660	50/60Hz

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 4 页 共 4 页

证书编号: 2014010304680069

纸号: 896315

型号的解释: (续)

代码	电压	频率	代码	电压	频率
G7	120	50/60Hz	Y7	690	50/60Hz
FC7	127	50/60Hz	JD	12	DC
GC7	140	50/60Hz	ZD	20	DC
L7	200	50/60Hz	BD	24	DC
LE7	208	50/60Hz	BND	32	DC
M7	220	50/60Hz	CD	36	DC
P7	230	50/60Hz	ED	48	DC
U7	240-230	50/60Hz-50Hz	ND	60	DC
W7	277	50/60Hz	SD	72	DC
Q7	380	50/60Hz	DD	96	DC
KD	100	DC	LD	200	DC
FD	110	DC	MD	220	DC
GD	125	DC	UD	250	DC
PD	155	DC	TD	305	DC
OD	174	DC	VD	348	DC
			RD	440	DC

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

