



CERTIFICATE

No. Z1 105732 0012 Rev. 00

Model(s): EPDU1016S(###)(+), EPDU1016SX(a)(b)(c)0(###)(+)
 (See page 2 for details of model description)

Brand Name: APC



Parameters:

Rated input: 200-240VAC, 50/60Hz, 16A
 Rated output: 200-240VAC, 16A total
 Protection class: I
 Degree of protection: IP20

Model description

(a)(b)(c) meanings			
(a): Qty of C13 outlets	(b): Qty of C19 outlets	(c): Qty of Germany standard outlet (DIN49440-SCHUKO)	0: detachable type
0: 0C13	0: 0C19	0:0	-
1:2C13	1:1C19	1:2	
2:4C13	2:2C19	2:4	
3:6C13	3:3C19	3:6	
4:8C13	4:4C19	4:8	
	5:6C19		
C13:10A per outlet C19:16A per outlet DIN49440-SCHUKP:16A per outlet Total numbers of outlets for each model ≤ 8			
(###) means customer types, # may be 0-9			
(+) may be Blank, without lockable outlet socket -L, with lockable outlet socket			





Product Service

CERTIFICATE

No. Z1 105732 0012 Rev. 00

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 105471