



Product Service

CERTIFICATE

No. Z1 105732 0013 Rev. 00

Holder of Certificate: **Schneider Electric IT (China) Co., Ltd.**
A2, No.25 factory, New Development District
No. 30 Futedong Third Road
Waigaoqiao Free Trade Zone
201203 Shanghai
PEOPLE'S REPUBLIC OF CHINA

Certification Mark:




Product: **ITE equipment**
EasyPDU Switched

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 704202019103-00

Valid until: 2025-05-25

Date, 2020-05-27


(Bin Li)

CERTIFICATE

No. Z1 105732 0013 Rev. 00

Model(s): EPDU1116S (###) (+); EPDU1132S (###) (+);
EPDU1116SX(a)(b)(c)(dd) (###) (+);
EPDU1132SX(a)(b)(c)(dd) (###) (+)

Brand Name: APC



Parameters:

For EPDU1116S (###) (+); EPDU1116SX(a)(b)(c)(dd) (###)(+):
Rated input: 200-240VAC, 50/60Hz, 16A
Rated output: 200-240VAC, 16A total

For EPDU1132S (###) (+); EPDU1132SX(a)(b)(c)(dd) (###) (+):
Rated input: 200-240VAC, 50/60Hz, 32A
Rated output: 200-240VAC, 16A per bank, 32A total
Protection class: I
Degree of protection: IP20

Model description

Model	Max Input Current	Output parameter	Connection method	Cord Length	Socket outlets (Qty)	Circuit Breakers	Mount Style	Max WxHxD (mm)	Max Weight
EPDU1116S (###)(+)	16A	16A total	Non-detachable cord	3m	C13(20pcs) C19(4pcs)	NA	Vertical	55x1738x62	7.3
EPDU1132S (###)(+)	32A	32A total	Non-detachable cord	3m	Bank 1:C13(10pcs) C19(2pcs) Bank 2:C13(10pcs) C19(2pcs)	2(pcs) 16A	Vertical	55x1738x62	7.9
EPDU1116SX (a)(b)(c)(dd) (###)(+)	16A	16A total	Non-detachable cord	<10m	according to nomenclature's rule	NA	Vertical	55x1738x62	9
EPDU1132SX (a)(b)(c)(dd) (###)(+)	32A	32A total	Non-detachable cord	<10m	according to nomenclature's rule	2(pcs) 16A	Vertical	55x1738x62	9

nomenclature's rule

CERTIFICATE

No. Z1 105732 0013 Rev. 00

(a)(b)(c)(dd) Maybe			
(a): Qty of C13 outlets	(b): Qty of C19 outlets	(c): Qty of Germany standard outlet (DIN49440-SCHUKO)	(dd): Cord Length
0: 0C13	0: 0C19	0:0SCH	d may be 0-9
1:8C13	1:1C19	1:2SCH	
2:12C13	2:2C19	2:4SCH	
3:14C13	3:3C19	3:6SCH	
4:16C13	4:4C19	4:8SCH	
5:18C13	5:6C19	5:10SCH	
6:20C13	6:12C19	6:12SCH	
7:24C13		7:16SCH	
		8: 18SCH	
		9: 24SCH	
C13:10A per outlet C19:16A per outlet DIN49440-SCHUKO:16A per outlet Total numbers of outlet for each model ≤ 24			
(###) means customer types, # may be 0-9			
(+) may be Blank, without lockable outlet socket -L, with lockable outlet socket			

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 105471