



NWGQ.E177299 Information Technology Equipment Including Electrical Business Equipment

[Page Bottom](#)

Information Technology Equipment Including Electrical Business Equipment

[See General Information for Information Technology Equipment Including Electrical Business Equipment](#)

AMERICAN POWER CONVERSION CORP

E177299

132 FAIRGROUNDS RD
PO BOX 278
WEST KINGSTON, RI 02892 USA



Trademark and/or Tradename:

Accessory - Power Distribution Modules, Model(s) PDM1320IEC-3P-1-xxxx, PDM1320L5-3P-1-xxxx

Accessory mobile surge protectors, Model(s) Pnote Pro 3-LH, Pnote Pro3

Accessory power modules, Model(s) AP9510515, AP9510520, AP9510L630, PM20-5-15, PM20-5-20, PM20-6-30

Automatic transfer switches, Model(s) AP7701, AP7701X298, AP7750, AP7751

Battery packs, Model(s) UPB60

Computer matrix switch accessories, Model(s) AP5639

Computer matrix switch accessory interface pods, Model(s) AP5630, AP5631, AP5632, AP5633, AP5634, AP5635, AP5636, AP5637, AP5638

Computer matrix switch systems, Model(s) AP5603

Electronic rack access systems, Model(s) AP9360, AP9361

Enviromental management units (EMU III), Model(s) AP9340, AP9350, NBRK0200

Environmental room managers, Model(s) AP9320, AP9321

Hot aisle containment systems, Model(s) InfraStruXure Computer Room, InfraStruXure HD, InfraStruXure Telecommunications Room, InfraStruXure Type A, InfraStruXure Wiring Closet, ISX HD

In-line Current Monitor, Model(s) QDH23197-3C1G, QDH23197-3R1G, QDH23197-4C1G, QDH23277-2C1G, QDH23277-2R1G

KVM switches, Model(s) AP5201, AP5202

Master switch power receptacles, Model(s) AP95103202

Mobile surge protectors, Model(s) PnoteProC6, PnoteProC6-EC, PnoteProC8, PnoteProC8-EC

Modular Power Distribution Unit, Model(s) PDPM138H-5U, PDPM288G6H

Multiple PC/server digital access KVM switches, Model(s) AP5601, AP5602, AP5610, AP5611, AP5615, AP5616

NetBotz Rack Monitor 450/550, Model(s) NBRK0450, NBRK0550

Network interface devices, Model(s) Powershield HFC UPS

Power Distribution Modules, Model(s) 00P3781, PDM3450CS50-xxxx, PDM3520IEC309-xxxx, PDM3520L2120-xxxx, PDM3520L2130-xxxx

Power distribution systems, Model(s) InfraStruXure, Power StruXure System

Power distribution units, Model(s) OG-PD150G6F, OG-PD150L6F, OG-PD40F6FK1-M, OG-PD40G6FK1-M, OG-PD40L6FK1-M, OG-PD60F6FK1, OG-PD60G6FK1, OG-PD60L6FK1, OG-PD80F6FK1-M1, OG-PD80G6FK1-M1, OHR609, OT834, OTP603, 1T890, 1T891, 3T765, 5T436, 5T437, AP6037, AP6039, AP7516, AP7530, AP7532, AP7540, AP7541, AP7557NA, AP7562, AP7563, AP7564, AP7567, AP7567A, AP7568, AP7569, AP7592, AP7593, AP7594, AP7598, AP7599, AP7610, AP7800, AP7801, AP7802, AP7811, AP7815, AP7820, AP7821, AP7830, AP7831, AP7832, AP7840, AP7841, AP7862, AP7863, AP7864, AP7864 QAA73813, AP7866, AP7866A, AP7867, AP7867A, AP7868, AP7869, AP7892, AP7893, AP7894, AP7898, AP7899, AP7900, AP7901, AP7902, AP7911, AP7920, AP7921, AP7930, AP7931, AP7932, AP7940, AP7941, AP7960, AP7961, AP7961X364, AP7968, AP7990, AP7991, AP7998, AP9328, AP9553, AP9554, AP9558, AP9559, AP9560, AP9561, AP9565, AP9566, AP9568, AP9570, AP9571, AP9572, AP9590, APC-AP6015/DELL- OT834, APC-AP6016/ DELL-5T346, APC-AP6020/ DELL-1T890, APC-AP6021/ DELL-1T891, APC-AP6030/DELL-3T767, APC-AP6031/DELL-5T439, APC-AP6035/DELL-M1044, APC-AP6120/DELL-5T437, APC-AP6121/DELL-3T765, DELL6015, DELL6016, DELL6020, DELL6030, DELL6031, DELL6037, DELL6039, DELL6120, EMC9571, G761N, G789N, G791N, H579N, J541N, K558N, NGRPDM30-1, NGRPDM30-3, NGRPDM60-3, NGRPDMFIELD, NGRPDS-4, NGRPDS-6

Power strips, Model(s) AP7862X135, AP7863X135, AP7863X414

PRM chassis, Model(s) PRM24

PSX information controllers, Model(s) AP2200, AP92100, AP9420, AP9421, AP9422, AP9423

Rack Distribution Panel, Model(s) PDPM72F-5U

Rack Power Panel, Model(s) PDPM144F, PDPM288H

Rack-mount distribution panels, Model(s) OG-RDP

Rack-mounted monitor and key boards, Model(s) AP5015, AP5017, AP5017J

Remote power panels, Model(s) OG-PDRPPNX10, OG-PDRPPNX20, OG-PDRPPNX10-M

Universal notebook batteries, Model(s) UPB70, UPB80, UPB80i, UPB90

Vertical console port servers, Model(s) AP9290

xxxx - length of Output Powercord in cm, max. 1040 cm

Last Updated on 2009-05-29

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2009 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered

under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2009 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

