


CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product Produit	Enclosure for fixed installation for protective devices and power dissipating equipments
Name and address of the Applicant Nom et adresse du demandeur	SCHNEIDER ELECTRIC INDUSTRIES SAS ELECTROPOLE 31 RUE PIERRE MENDES FRANCE, EYBENS 38050 GRENOBLE CEDEX 9 France
Name and address of the manufacturer Nom et adresse du fabricant	SCHNEIDER ELECTRIC INDUSTRIE ITALIA SPA VIA CIRCONVALLAZIONE EST 1 24040 STEZZANO BG Italy
Name and address of the factory Nom et adresse de l'usine	SCHNEIDER ELECTRIC INDUSTRIE ITALIA SPA VIA CIRCONVALLAZIONE EST 1 24040 STEZZANO BG Italy
Rating and principal characteristics Valeurs nominales et caractéristiques principales	-25°C / +60°C - IP40 (see Additional Sheet)
Trademark (if any) Marque de fabrique (si elle existe)	 Schneider Electric
Type of manufacturer's Testing Laboratories used Type de programme de laboratoire d'essais constructeur	
Model / Type Ref. Réf. de type	Series Mini Pragma (see Additional Sheet)
Additional information (if necessary may also be reported on page 2) Les informations complémentaires (si nécessaire, peuvent être indiquées sur la 2ème page)	-
A sample of product was tested and found to be in conformity with IEC Un échantillon de ce produit a été essayé et été considéré conforme à la CEI	60670-1(ed.1);am1 60670-24(ed.2)
National differences / Comments Les différences nationales / Commentaires	EU Group Differences
As shown in the test report Ref. No. which forms part of this certificate Comme indiqué dans le rapport d'essais numéro de référence qui constitue partie de ce certificat	MI15A0492659-02

This CB Test Certificate is issued by the National Certification Body:

Ce Certificat d'essai OC est établi par l'Organisme National de Certification

 IMQ S.p.A.
 Via Quintiliano 43 I-20138 Milano, Italy


DESCRIPTION OF SERIES Mini Pragma

Type ref.	Cat. ref.	Description: number of modules / DIN rail	Dimensions H x W x D (mm)
MIPS104yy	MIPxx104y	4 / 1	198x124x95,5
MIPS106yy	MIPxx106y	6 / 1	198x160x95,5
MIPS108yy	MIPxx108y	8 / 1	198x196x95,5
MIPS112yy	MIPxx112y	12 / 1	228x268x102
MIPS118yy	MIPxx118y	18 / 1	228x376x103
MIPS212yy	MIPxx212y	24 / 2	353x268x102
MIPS312yy	MIPxx312y	36 / 3	478x268x102