



产品认证证书

证书编号: CQC2007010304228095

申请人名称及地址

施耐德电气(中国)有限公司上海分公司
上海市普陀区绥德路669号

制造商名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

Schneider Electric a. s. (V046458)
Cizovska 447 - 39701 Pisek - Czech Republic

产品名称和系列、规格、型号

信号灯

XVB: Ui:250V; Uimp:4kV; 白炽灯:Ue: AC12-48V,AC48-230V; LED:Ue:AC/DC24V, AC120V,AC230V; 放电管:Ue:AC/DC24V,AC120V,AC230V,AC48V,DC48V; 蜂鸣器:Ue:AC/DC12-48V,AC120-230V; IP65(安装在固定基座)、IP66(直接安装在基座单元); 型号解释见附件

产品标准和技术要求

GB/T 14048.5-2017

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求, 特发此证。

发证日期: 2020年08月25日 有效期至: 2025年08月05日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0372773



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2007010304228095

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND ADDRESS OF THE FACTORY

Schneider Electric a. s. (V046458)
Cizovska 447 - 39701 Pisek - Czech Republic

PRODUCT NAME, MODEL AND SPECIFICATION

Illuminated Beacon

XVB: Ui:250V; Uimp:4kV; Filament Lamp:Ue: AC12-48V,AC48-230V; LED:Ue:AC/DC24V, AC120V,AC230V;
Discharging Tube:Ue:AC/DC24V,AC120V,AC230V,AC48V,DC48V; Buzzer:Ue:AC/DC12-48V,AC120-230V; IP65 (Installed on
fixed base)、IP66 (Installed directly in the base unit)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification
rules of CQC11-462142-2019 .

Valid from: Aug.25,2020

Valid until: Aug.05,2025

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing
certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President: _____

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0372773



产品认证证书

附录

第 1 页 共 4 页

证书编号: CQC2007010304228095

纸号: 372773

型号解释:

白炽灯型号规格解释

$\frac{XVB}{I}$	$\frac{L}{II}$	$\frac{3}{III}$	$\frac{B}{IV}$	$\frac{3}{V}$
I -	产品系列号 XVB			
II -	外形 L - 灯塔, 直径 70 mm			
III -	灯泡型式和信号型式 3 - 白炽灯, 恒定光(仅适用 L 型) 4 - 白炽灯, 闪烁光(仅适用 L 型)			
IV -	电源电压 (仅适用于闪烁型) B - 24...48 V DC M - 48...230 V AC			
V -	镜片颜色 3 - 绿色 4 - 红色 5 - 琥珀色 6 - 蓝色 7 - 透明 8 - 黄色			

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 2 页 共 4 页

证书编号: CQC2007010304228095

纸号: 372773

LED型和放电管型号规格解释

	XVB I	L II	0 III	B IV	3 V
I-	产品系列号 XVB				
II-	形状 L-灯塔, 直径 70 mm C- 镜片或 底座 +外壳				
III-	灯泡型式和信号型式或其它 0- LED 串, 恒定光 Waiting for MD confirm(仅适用 L 型) 1- LED 串, 闪烁光 Waiting for MD confirm(仅适用 L 型) 6- 内置式放电管 SJ 8- 内置式放电管 10J 为 XVB 型 21- 底座+盖+垫圈 21A- 底座+盖+垫圈 侧面电缆插入 AS 界面 21B- 底座+盖+垫圈 底部电缆插入 M12 连接器 AS 界面				
IV-	电压 E-48VAC/DC G-120 V AC M-230 V AC				
V-	镜片颜色 3- 绿色 4- 红色 5- 琥珀色 6- 蓝色 7- 透明 8- 黄色				

发声单元型号规格解释

	XVB I	C9 II	B III
I-	产品系列号 XVB- 安装在 XVB 底座上		
II-	形状 C9- 蜂鸣器元件		
III-	电源电压 B-12...48 V AC/DC M-120...230 V AC		

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 3 页 共 4 页

证书编号: CQC2007010304228095

纸号: 372773

Description of the series Explanation about the model	Incandescent Pilot Light Models				
	XVB	L	3	B	3
	I	II	III	IV	V
I Series designation XVB					
II Shape L - Beacon 70 mm diameter					
III Type of bulb and type of signal or other 3 - Incandescent bulb, steady light (only for Shape L) 4 - Flashing with incandescent bulb (only for Shape L)					
IV Supply Voltage (for flashing type only) B - 24...48 VDC M - 48...230 VAC					
V Lens Color 3 - Green 4 - Red 5 - Amber 6 - Blue 7 - Clear 8 - Yellow					

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 4 页 共 4 页

证书编号: CQC2007010304228095

纸号: 372773

Description of the series Explanation about the model	LED Cluster models and built-in strobe models				
	XVB I	L II	0 III	B IV	3 V
I Series designation XVB					
II Shape L - Beacon 70 mm diameter C - Lens or base + cover for bank					
III Type of bulb and type of signal or other 0 - LED cluster, steady light (only for Shape L) 1 - LED cluster, flashing (only for Shape L) 6 - Built-in strobe 5J 8 - Built-in strobe 10J for XVB type 21 - Base + cover + gasket 21A - Base + cover + gasket with side cable entry for AS-Interface 21B - Base + cover + gasket with bottom entry, pre-cabled and fitted with M12 and connector for AS-Interface					
IV Supply Voltage (for flashing type only) E - 48VAC/DC G - 120 VAC M - 230 VAC					
V Lens Color 3 - Green 4 - Red 5 - Amber 6 - Blue 7 - Clear 8 - Yellow					

Description of the series Explanation about the model	Audible signal units		
	XVB I	C9 II	B III
I Series designation XVB - For mounting on XVB base			
II Shape C9 - Buzzer element			
III Supply voltage B - 12...48 VAC/DC M - 120...230 VAC			

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>