



# Certificate of Compliance

**Certificate:** 2191023

**Master Contract:** 225619

**Project:** 70014332

**Date Issued:** November 28, 2014

**Issued to:** Telemecanique/Schneider Electric

**Industries SAS.  
BP 660  
Zone Industrielle No. 3  
L'Isle d'Espagnac, 16340  
France  
Attention: Yukihsa Fujimoto**

*The products listed below are eligible to bear the CSA Mark shown*



*Pierre-Yves Despatis*

**Issued by:** Pierre-Yves Despatis

## **PRODUCTS**

**CLASS 3211 05 - INDUSTRIAL CONTROL EQUIPMENT - Motor Controllers - Manual**

Beacons lights, open type, LED Tower, may be provided with sound alarm:

Model XVC1B followed by 1, 2, 3, 4 or 5, may be followed by K or S, may be followed by K or T, may be followed by T, , may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 24 V dc, Class 2, 550 mA max.

Model XVC1B, followed by 1, 2 or 3, followed by H, followed by K, may be followed by T, , may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 24 V dc, Class 2, 660 mA max.

Model XVC4B, followed by digit 1 through 5, may be followed by 5S, K or T, may be followed by K or T, may be followed by T, , may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 24 V ac/dc, Class 2, 165 mA max.

Model XVC6B followed by digit 1 through 5, may be followed by 5S, K or T, may be followed by K or T, may be followed by T, may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 24 V ac/dc, Class 2, 165 mA max.

Model XVC1M followed by 1, 2, 3, 4 or 5, may be followed by K or S, may be followed by K or T, may be followed by T, may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 100-240 V ac, 280 mA max.



**Certificate:** 2191023

**Master Contract:** 225619

**Project:** 70014332

**Date Issued:** November 28, 2014

---

Model XVC1M, followed by 1, 2 or 3, followed by H, followed by K, may be followed by T, may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 100-240 V ac, 320 mA max.

Model XVC4M followed by 1, 2, 3, 4 or 5, may be followed by 5S or T, may be followed by T, may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 100-240 V ac, 110 mA max.

Model XVC6M, followed by 1, 2, 3, 4 or 5, may be followed by 5S, K or T, may be followed by K or T, may be followed by T, may be followed by 1 digit to 5 digits any letters (R, O, G, B or C), followed by Q, rated input supply 100-240 V ac, 115 mA max.

Notes:

1. These devices are LED Sign Towers intended to be used in industrial applications, Type 1 environment.
2. Certified as open type devices for use only in Certified equipment where the acceptability of combination is to be determined by CSA International.

**APPLICABLE REQUIREMENTS**

CSA-C22.2 No. 14-13 - Industrial Control Equipment