



Ref. Certif. No.

US-35668-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

NetBotz Rack Monitor

Name and address of the applicant

SCHNEIDER ELECTRIC IT CORPORATION,
FKA APC AMERICAN
POWER CONVERSION
132 FAIRGROUNDS RD
PO BOX 278
WEST KINGSTON RI 02892 USA

Name and address of the manufacturer

SCHNEIDER ELECTRIC IT CORPORATION,
FKA APC AMERICAN
POWER CONVERSION
132 FAIRGROUNDS RD
PO BOX 278
WEST KINGSTON RI 02892 USA

Name and address of the factory

AMERICAN POWER CONVERSION CORPORATION (A.P.C.) B.V.
CAVITE 2 - LOT 10 BLOCK 16 PHASE IV PEZA ROSARIO 4106
CAVITE
PHILIPPINES

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

NBRK0250, NBRK0570, NBRK0750

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.
 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E177299-A6007-CB-1 issued on 2020-06-01

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-06-01

Signature:

Original Issue Date: 2020-04-27

Jolanta M. Wroblewska



Ref. Certif. No.

US-35668-M1-UL

Ratings:

NBRK0250

Input: 100-240VAC, 50/60Hz, 10A

Output: 100-240VAC, 50/60Hz, 10A Max.

NBRK0570

Input: 100-240VAC, 50/60Hz, 2A

NBRK0750

Input: 100-240VAC, 50/60Hz, 10A

Output: 100-240VAC, 50/60Hz, 10A Max.

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

- Addition of fuses. Limited testing conducted.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-06-01

Original Issue Date: 2020-04-27

Signature:

Jolanta M. Wroblewska