

CERTIFICATE FI/40954

Our Ref. HEL-CERT210200144-01



Product	Socket-outlet
Туре	270/***
Trademark	Schneider
Certificate Holder	Schneider Electric Industries SAS 35 Rue Joseph Monier, 92500, Rueil-Malmaison, France
Technical information	16 A; 250 V~; IP20/IP21/IP44; Standard sheet III
Other information	2P+E. One-fold flush-type fixed socket-outlet. With screw terminals. Screw- or claw fixing. Available with- or without shutters.
	See pages 2-5 for socket-outlet and frame type lists.
The product is certified according to the following standard(s)	SFS 5610:2015 + A11:2016 IEC 60884-1:2002 + A1:2006 + A2:2013
Validity	This certificate is valid until 2026-02-22 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.
Date of issue	2021-02-22
	SGS Fimko Ltd
Signature	Atim Shape

Joonas Leinonen Certification Manager

SGSSG

Page 1 of 5

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5



Page 2 of 5 to Certificate: FI/40954

Manufacturer	Schneider Electric Industries SAS 35 Rue Joseph Monier, 92500, Rueil-Malmaison, France
Manufacturing site	Merten GmbH Fritz-Kotz-Strasse 8, 51674, Wiehl, North Rhine-Westphalia, Germany
Additional information	The products have certificate SE-S-2002900 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.
	This certificate replaces previous certificate FI 30014, dated 2017-07-06. Renewal of the certificate.
As shown in the Test Report(s) No(s):	2019703STO-001
Socket-outlet type list:	

Antivandalism: (1-gang) 270/S1B7217902

System M-Creativ 270/2300-35

System M (Thermo/Duro) 270/2371, 270/2373, 270/2376, 270/2374, 270/2300, 270/2301, 270/2309 with or without LED light module 2003, 270/2474, 270/2485, 270/2496, 270/2470, 270/2471, 270/2472, 270/2473, 270/2334 with LED light module 2334

System Design (Thermo/Duro)

270/2375, 270/2377, 270/2372, 270/2379 with or without LED light module 2003, 270/2378, 270/2306, 270/2308, 270/2478, 270/2476, 270/2477

System Design (Thermo/Metal) 270/NHA2920902, 270/NHA2920902, 270/NHA292002, 270/NHA5195702

AQUADESIGN 270/2330, 270/2335

Renova 270/EAV54699



Page 2 of 5

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5



Page 3 of 5 to Certificate: FI/40954

Frame types:

System M: (Thermo+Duro) **M-Smart:** (1 - 5 gang) 4841, 4842, 4843, 4844, 4845

1M: (1 - 5 gang) 3891, 3892, 3893, 3894, 3895

M-Plan II: (1 - 3 gang) 4881, 5124, 4882, 5125, 4883, 5126

M-Plan: (1 - 5 gang) 4861, 4862, 4863, 4864, 4865

M-Plan Metall: (1 - 5 gang) 4751, 4752, 4753, 4754, 4755

M-Plan real glas: (1 - 5 gang) 4891, 4892, 4893, 4894, 4895

M-Plan real wood: (1 – 5 gang) 4051, 4052, 4053, 4054, 4055

Atelier-M: (1 - 5 gang) 3881, 3882, 3883, 3884, 3885

System M – Elegance: (1 - 5 gang) 4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035 4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

System M – Exxact (Thermo) Basic: (1 - 5 gang) BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

Design: (1 - 3 gang) BBV49558, BBV49559, BBV49561

Solid: (1 - 4 gang) BBV49558, BBV49559, BBV49561, BBV49589

Solid Glass: (1 - 4 gang) S1A45091, S1A45092, S1A45094, S1A45092

Combi: (1 - 5 gang) BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

Primo: (1 - 6 gang) BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

Page 3 of 5

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland **t.** +358 9 696 361 www.sgs.fi



Page 4 of 5 to Certificate: FI/40954

Gasket for all IP44 frames: (1 - 3 gang) BBV49557, S1A33102, S1A33103

System M – Creativ: (1 - 5 gang) 4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35

System M – M-Pure: (1 – 5 gang) 4010-36, 4020-36, 4030-36, 4040-36, 4050-36

System Design: (Thermo + Duro) **ARTEC, Antik, Fläche:** (1 - 5 gang) 4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

System Design: (Thermo + metal + glas/stone) **D-Life:** (1 – 5 gang) NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702

D-Life metal: (1 – 5 gang) NHA2923102, 2xNHA2923302, 2xNHA2923302/1xNHA2923502, 2xNHA2923302/2xNHA2923502,2xNHA2923302/3xNHA2923502

D-Life glas/basalt: (1 – 5 gang) NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

AQUADESIGN: (1 - 4 gang) 4011, 4012, 4013, 4014

Antivandalism: (1 – 3 gang) 4801, 4802, 4803

Renova Glass frame: (1 - 3 gang) BBV28342, BBV28343, BBV28344

Plastic frame: (1 - 5 gang) 101370, 101371, 101372

Page 4 of 5

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland t. +358 9 696 361 www.sgs.fi



Page 5 of 5 to Certificate: FI/40954

	Robust Screw-Type (270/***) Socket Outlets, IK class IK09.			Robust: frame
	Insert	Center Cover	Center Cover Adapter	
Without Shutters	270/***	101363	101599	101600 (1-gang)
With Shutters		EAV54699	44-0496786383555.0825-6385 54580496200000000000000000000000000000000000	

Insert	Center Cover (with Shutters)	Frames
4454554555566555668668668668666565566 5555555556655566	NVE66783	100520 (1-gang) 100521 (2-gang) 100522 (3-gang) 100523 (4-gang) 101524 (5-gang)
	 Providence of the second second	



Page 5 of 5

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland **t.** +358 9 696 361 www.sgs.fi