



中国国家强制性产品认证证书

证书编号: 2007010307236560

委托人名称、地址

上海施耐德工业控制有限公司
上海市普陀区绥德路629号

生产者(制造商)名称、地址

施耐德(泰国)低压电器有限公司
540 Soi 9 Bangpoo Industrial Estate, Sukhumvit Road, Muang District,
Samutprakarn 10280, Thailand

生产企业名称、地址

施耐德(泰国)低压电器有限公司
540 Soi 9 Bangpoo Industrial Estate, Sukhumvit Road, Muang District,
Samutprakarn 10280, Thailand

产品名称和系列、规格、型号

电动机断路器

GV2ME、GV2P、GV2L, 详见参数附件

产品标准和技术要求

GB 14048.2-2008, GB 14048.4-2010

上述产品符合强制性产品认证实施规则
CNCA-01C-011: 2007的要求, 特发此证。

发证日期: 2014年08月18日 有效期至: 2019年08月18日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2007年06月18日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 0978086



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2007010307236560

NAME AND ADDRESS OF THE APPLICANT

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suid Road, Putuo District, Shanghai, P.R. China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider (Thailand) Limited
540 Soi 9 Bangpoo Industrial Estate, Sukhumvit Road, Muang District,
Samutprakarn 10280, Thailand

NAME AND ADDRESS OF THE FACTORY

Schneider (Thailand) Limited
540 Soi 9 Bangpoo Industrial Estate, Sukhumvit Road, Muang District,
Samutprakarn 10280, Thailand

NAME, MODEL AND SPECIFICATION

Motor Circuit-breaker

GV2ME、GV2P、GV2L; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.2-2008, GB 14048.4-2010

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-01C-011:2007).

Date of issue: Aug. 18, 2014 Date of expiry: Aug. 18, 2019

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Jun. 18, 2007

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

Q 0978086



中国国家强制性产品认证证书

附录:

第 1 页 共 4 页

证书编号: 2007010307236560

纸号: 978086

GV2ME、GV2P、GV2L; 型号解释详见附录;

GV2ME

Ui: 690V

Ue: AC400V/415V, AC690V

In: 0.16A, 0.25A, 0.4A, 0.63A, 1.0A, 1.6A, 2.5A, 4.0A, 6.3A, 10A, 14A, 18A, 23A, 25A, 32A

过电流脱扣器类型: 热磁式;

AC400V/415V:	Icu=10kA	Ics=50%Icu (In=32A)
	Icu=15kA	Ics=40%Icu (In=23A, 25A)
	Icu=15kA	Ics=50%Icu (In=14A, 18A)
	Icu=100kA	Ics=100%Icu (In=0.16A~10A)
AC690V:	Icu=3kA	Ics=75%Icu (In=2.5A~32A)
	Icu=100kA	Ics=100%Icu (In=0.16A~1.6A)

脱扣级别: 10A

使用类别: A;

极数: 3P

GV2P

Ui: 690V

Ue: AC400V/415V, AC690V

In: 0.16A, 0.25A, 0.4A, 0.63A, 1.0A, 1.6A, 2.5A, 4.0A, 6.3A, 10A, 14A, 18A, 23A, 25A, 32A

过电流脱扣器类型: 热磁式;

AC400V/415V:	Icu=50kA	Ics=50%Icu (In=18A~32A)
	Icu=100kA	Ics=100%Icu (In=0.16A~14A)
AC690V:	Icu=4kA	Ics=100%Icu (In=18A~32A)
	Icu=6kA	Ics=100%Icu (In=6.3A~14A)
	Icu=8kA	Ics=100%Icu (In=2.5A~4A)

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 4 页

证书编号: 2007010307236560

纸号: 978086

$I_{cu}=100kA$ $I_{cs}=100\%I_{cu}$ ($I_n=0.16A\sim1.6A$)

脱扣级别: 10A

使用类别: A,

极数: 3P

GV2L

U_i : 690V

U_e : AC400V/415V, AC690V

I_n : 0.4A, 0.63A, 1.0A, 1.6A, 2.5A, 4.0A, 6.3A, 10A, 14A, 18A, 25A, 32A

过电流脱扣器类型: 热磁式,

AC400V/415V: $I_{cu}=50kA$ $I_{cs}=50\%I_{cu}$ ($I_n=14A\sim32A$)

$I_{cu}=100kA$ $I_{cs}=100\%I_{cu}$ ($I_n=0.4A\sim10A$)

AC690V: $I_{cu}=4kA$ $I_{cs}=75\%I_{cu}$ ($I_n=1.6A\sim32A$)

$I_{cu}=100kA$ $I_{cs}=100\%I_{cu}$ ($I_n=0.4A\sim1.0A$)

脱扣级别: 10A

使用类别: A,

极数: 3P

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 3 页 共 4 页

证书编号: 2007010307236560

纸号: 978086

型号的解释:

	<u>GV2-</u>	<u>ME</u>	<u>01</u>	<u>6</u>
	I	II	III	IV
	GV2-ME 、 GV2-P			GV2-L
I	电动机断路器基本型号			电动机断路器基本型号
II	操动器类型 ME - 按钮操作, 具有过载, 短路保护功能 P - 旋转手柄操作, 具有过载, 短路保护功能			操动器类型 L - 旋转手柄操作, 具有短路保护功能
III	电流规格设定范围: 01 - 0.10 to 0.16A 02 - 0.16 to 0.25A 03 - 0.25 to 0.40A 04 - 0.40 to 0.63A 05 - 0.63 to 1.0A 06 - 1.0 to 1.6A 07 - 1.6 to 2.5A			电流规格设定范围: 03 - 0.40A 04 - 0.63A 05 - 1.0A 06 - 1.6A 07 - 2.5A 08 - 4.0A 10 - 6.3A

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 4 页 共 4 页

证书编号: 2007010307236560

纸号: 978086

08 - 2.5 to 4.0A
 10 - 4.0 to 6.3A
 14 - 6 to 10A
 16 - 9 to 14A
 20 - 13 to 18A
 21 - 17 to 23A
 22 - 20 to 25A
 32 - 24 to 32A

14 - 10A
 16 - 14A
 20 - 18A
 22 - 25A
 32 - 32A

IV

连接形式:

不适用

空白: 卡轨和螺钉连接

6. 环形接线片连接 (仅 GV2-ME)

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

