



# Certificate of Compliance

**Certificate:** 1662126 (LR 63938C)

**Master Contract:** 157869

**Project:** 2142864

**Date Issued:** 2009/04/10

**Issued to:** American Power Conversion Corp.

85 Rangeway Rd Bldg 2  
North Billerica, MA 01862  
USA  
Attention: John Coviello

*The products listed below are eligible to bear the CSA Mark shown*



**Issued by:** James Cotton

**Authorized by:** David Schaefer, Manager of  
Certification Services

## **PRODUCTS**

**CLASS 5311 08** - POWER SUPPLIES - Uninterruptible Power Systems

Uninterruptible Power Supplies

Cord-connected models:

J10, rated 120Vac,60Hz, 12A input; 120Vac, 47-63Hz, 1000VA, 600W, 9A output.

J15, rated 120Vac,60Hz, 12A input; 120Vac, 47-63Hz, 1440VA, 865W, 12A output.

S10, rated 120Vac,47-63Hz, 12A input; 120Vac, 47-63Hz, 1000VA, 700W, 9A output.



**Certificate:** 1662126 (LR 63938C)

**Master Contract:** 157869

**Project:** 2142864

**Date Issued:** 2009/04/10

---

S15, RLC1080, rated 120Vac,47-63Hz, 12A input; 120Vac, 47-63Hz, 1440VA, 1000W max.,12A output.

S20, S20XXXXXXXXXX, CEN-UPS1250XXXXXXXXXX, rated 120Vac,47-63Hz, 12A input; 120Vac, 47-63Hz, 1440VA, 1250W output.

**NOTES**

- Models may be provided with the suffix “BLK”.
- The “X” placeholder may be replaced by any alphanumeric character, “-” character or blanks.

**APPLICABLE REQUIREMENTS**

CSA C22.2 No. 107.3-05      Edition 2      Uninterruptible Power Systems (Includes Update 1)

Note : CSA Standard C22.2 No. 107.3-05 is harmonized with UL Standard 1778, Edition 4.

**MARKINGS**

See Descriptive Report