



Certification Record

CUSTOMER	CLASS	FILE
American Power Conversion Corp. 85 Rangeway Rd Bldg 2, North Billerica MA 01862 USA	5842-85 CORD SETS - Cord connected Multiple Receptacle Extension Boxes-Certified to US Standards	102418_0_000
	Refer to Class Description for program details	

TO THE REQUIREMENTS OF UL 1363 and UL 1449 (3rd Edition):

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 400V ac L-N, 500V ac L-G and N-G), cat. nos. C2 and C2C, rated 15A, 125V ac, 60Hz.

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 600V ac L-N and N-G, 700V ac L-G), cat. no. C3 and C3BLK, rated 15A, 125V ac, 60Hz.

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 600V ac L-N and N-G, 700V ac L-G), cat. no. C5 and C5BLK, rated 15A, 125V ac, 60Hz.

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 400V ac L-N, 600V ac L-G and N-G) cat. no. G5 and G5BLK, rated 15A, 125V ac, 60Hz.

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 400V ac L-N, 500V ac L-G and N-G), cat. nos. P8T3, P8T3-CN, P8VT3, P11VT3, P11VT3-CN, P11VT3MP6, P11VT3MP10-CN, P11VNT3, P11VNT3-CN and P11GTV, rated 15A, 125V ac, 60Hz.

Cord connected multiple receptacle extension box (relocatable power taps), Type 3 SPD (Voltage Protection Rating: 500V ac L-N and N-G, 600V ac L-G), cat. nos. P8V, P8VX577, P8VNTG and P8VNTGX578, rated 15A, 125V ac, 60Hz. Cord Connected Multiple Outlet Extension Boxes, rated at 15A, 120V ac, 60Hz, Type 3 SPD:- Models PER7, PER7T with VPR 400V ac L-N, 500V ac L-G and N-G;

- Models NET7, NET7T, PRO7, and PRO7T with VPR 330V ac L-N, 500V ac L-G and N-G;
- Models PER8 and PER8T with VPR 500V ac L-N, L-G, N-G;
- Models NET8, NET8N, PRO8, PRO8T2 with VPR 500V ac L-G, 400V ac L-N and N-G;
- Model NET9RMBLK with VPR 400V ac L-N, 500V ac L-G and N-G.

Cord Connected Multiple Receptacle Extension Box, with Transient Voltage Surge Suppression (Type 3 SPD; SUPPRESSED VOLTAGE RATING: 400V PEAK, L-N, N-G, 500V PEAK L-G), Cat Nos. CNS7Txx, P7Txx, P7VR, P7T6R, P7X, P74MP4 and P7V (where 'xx' represents the length of the power supply cord), rated 15A, 125V ac, 60Hz.

Cord Connected Multiple Receptacle Extension Box, Series P6, with Transient Voltage Surge Suppression (Type 3 SPD; SUPPRESSED VOLTAGE RATING: 400V PEAK, L-N, N-G, 500V PEAK L-G), Cat. Nos. P6H, P6B, P6BMP4 and CNS64, rated 15A, 125V ac, 60Hz.

Cord Connected Multiple Receptacle Extension Box, Cat. No. CNS63 rated 15A, 120V ac, has Surge Protection of 400V provided only Line-to-Neutral.

Cord Connected Multiple Receptacle Extension Box, PDIY series, with Surge Protection (Type 3 SPD; Voltage Protection Rating: 400V PEAK, L-N, N-G, 500V PEAK L-G), Cat. Nos. PDIY7, PDIY8, rated 15A, 125Vac, 60Hz

Notes:

1. The catalogue numbers under this report may be provided with suffix 'XX' where XX is any alphanumeric character to denote marketing and or packaging differences, no changes are made to the product.
2. The above catalogue numbers may be provided with suffix '-CN' to denote bilingual markings.

TO THE REQUIREMENTS OF UL 1363 AND UL 1449 (2nd EDITION):

- Cord connected multiple outlet extension box with Transient Voltage Surge Suppression (SUPPRESSED VOLTAGE RATING: 330V PEAK, L-N, L-G, N-G), Cat. Nos. P7GT, rated 15A, 120V ac, 60Hz.
- Cord Connected Multiple Outlet Extension Boxes, rated at 15A, 120V ac, 60Hz:
Surge Arrest with transient voltage surge protection (SUPPRESSED VOLTAGE RATING: 330V PEAK, L-N, L-G, N-G), Model Nos PER7, PER7T, PRO7, PRO7T, NET7, NET7T, NET8, NET9RM, PRO8, PRO8T2, PRO8T2C, PRO8T2MP12B,-PER8, PER8T.

/ao.

Copyright © 2014 CSA International. All rights reserved.