



Certificate of Compliance

Certificate: 1718289 (LR 63938C)

Master Contract: 157869

Project: 70052526

Date Issued: January 4, 2016

Issued to: American Power Conversion Corp.

800 Federal Street
Andover, MA 01810
USA
Attention: Bill Burks

The products listed below are eligible to bear the CSA Mark shown



Sam Zaffino

Issued by: Sam Zaffino

PRODUCTS

CLASS 5311 05 - POWER SUPPLIES - Stand-alone

Uninterruptible Power Supplies;

Model:	Input Rating:	Output Rating:
SMT2200, SUA2200US, SUA2200RMUS, SMT2200RM2U, DLT2200	120V, 60Hz, 19A	120V, 60Hz, 2200VA, 1980W
SMT3000, SUA3000US, SMT3000RM2U, DLT3000RM2U	120V, 60Hz, 24A	120V, 60Hz, 2880VA, 2700W
SUA3000R2IX38	220-240V, 60Hz, 16A	220-240V, 60Hz, 3000VA, 2700W
Smart-Ups-Ups 450, 450D	120V, 50/60Hz, 7A	120V, 50/60Hz, 280W, 3.75A
Smart-Ups-Ups 700X93, 700RMX176	120V, 50/60Hz, 7A	120V, 50/60Hz, 450W, 5.8A
SU700RMXLNET	120V, 50/60Hz, 12A	120V, 50/60Hz, 450W
SU700X167	120/230V, 60Hz, 10A	120V, 60Hz, 450W, 700VA
SU700R2IX38	220-240V, 60Hz, 7A	220-240V, 60Hz, 450W, 700VA, 3.2A
SU1000RMXLNET, SUA1000US	120V, 50/60Hz, 12A	120V, 50/60Hz, 670W
SU1000X93, SU1000RMX93, SU1000RMX176, SMT1000RM2U	120V, 60Hz, 10A	120V, 60Hz, 670W, 1000VA
SMC10002U	120V, 50/60Hz, 12A	120V, 50/60Hz, 950W



Certificate: 1718289 (LR 63938C)

Master Contract: 157869

Project: 70052526

Date Issued: January 4, 2016

SU1400X145, SU1400RMX106, SU1400X106, SU1400RMXLBX120, SU1400RMIX134, SU1400R2UX93, SU1400RMX93, SU1400RMX176, SU1400R2X217, SU1400X93, SU1400R2X180		
SU1500RMX155	120V, 60Hz, 15A	120V, 60Hz, 1100W, 1500VA
SU2000RMX155	120V, 60Hz, 20A	120V, 60Hz, 1450W, 2000VA
SU2200XLTX153	208V, 60Hz, 14A	208V, 60Hz, 1600W, 2200VA, 10.57A, 120V, 60Hz, 400W, 400VA, 3.3A
SU2200R3X167	120/230V, 60Hz, 25A	120V, 60Hz, 1600W, 2200VA
SU2200RMI3U	220-230V, 60Hz, 14A	196-253V, 60Hz, 1650W, 2200VA
SU2200RMBX120, SU2200X93, SU3000R3X145, SU3000RMBX120, SU3000X93, SU3000RMBX93	120V, 50/60Hz, 21/24/28A max	120V, 50/60Hz, 2200/2200/3000VA max, 1600/1600/2250W max
SUA1000IX38, SUA1000I	220-240V, 60Hz, 7A	220-240V, 60Hz, 670W, 1000VA, 4.5A
SUA1500IX38, SUA1500I	220-240V, 60Hz, 7A	220-240V, 60Hz, 980W, 1500VA, 6.8A
SUA1500US, SUA1500	120V, 50/60Hz, 12A	120V, 50/60Hz, 980W, 1400VA
SUA2200RMXL3U	110/120Vac, 60Hz, 24A	120Vac, 60Hz, 2200VA, 1980W, 19A
SUA3000RMUS, DLA3000	120V, 60Hz, 24A	120V, 50/60Hz, 2880VA, 2700W
SUA3000RT2X136	100V ac, 60Hz, 30A	100V ac, 60Hz, 2700W, 3000VA, 30A
SUA3000RMXL3U	110/120Vac, 60Hz, 24A	120Vac, 60Hz, 3000VA, 2700W, 24A
SUA5000RMT5U	208Vac, 60Hz, 24A	208Vac, 60Hz, 5000VA, 4000W, 22A
SURTA1500RMXL2U, SURTA1500RMXL2U-NC	120V, 60Hz, 12A	120V, 60Hz, 1050W, 1500VA, 12A
SURTA2000RMXL2U	120V, 60Hz, 16A	120V, 60Hz, 1400W, 2000VA, 16A
SURTA3000RMXL3U, SURTA3000RMXL3U-NC	120V, 60Hz, 24A	120V, 60Hz, 2100W, 3000VA, 24A
DLRTA3000RMXL3U		
SURTD3000RMXL3U	200-240V, 60Hz, 16A	200-240V, 60Hz, 2100W, 3200VA, 16A



Certificate: 1718289 (LR 63938C)

Master Contract: 157869

Project: 70052526

Date Issued: January 4, 2016

SURTD5000RMXLT3U, SURTD5000RMXLP3U, SURTD5000RMXLJP3U, DLRTD5000RMXL3U	200/208/220/240V, 50-60Hz, 24A	200-240V, 50-60Hz, 3500W, 25A
SURT6000RMXLT3U, SURTD6000RMXLP3U, SURTD6000RMXLJP3U, EMC6000R3XLU	200/208/220/240V, 50-60Hz, 20A (30A for hardwired)	200-240V, 50-60Hz, 4200W, 29A
SURT8000RMXLT6U, DLRT8000RMXLT6U	200-240V, 60Hz, 44A	200-240V, 60Hz, 6.4kW, 8kVA, 50A
SURT10000RMXLT6U	200-240V, 60Hz, 50A	200-240V, 60Hz, 8.0kW, 9.6kVA, 48A
SURT192RMXLBP3U	12Vdc, 60Hz, 5Ah	
SURTA48RMXLBP2U	48Vdc, 60Hz, 7.2Ah	
SURT48RMXLBP2U	48Vdc, 60Hz, 7.2Ah	
SMT750RM2U, SMT750RM2UNC	120V, 60Hz, 12A	120V, 60Hz, 750VA, 480W
SMT1500RM2U, SMC15002U, DLT1500RM2U	120V, 60Hz, 12A	120V, 60Hz, 1440VA, 980W
SMT3000RMT2U	208V, 60Hz, 16A	208V, 60Hz, 3000VA, 2700W
SURTA2200RMXL2U-NC	120V,50/60Hz,16A	120V,50/60Hz,1600W,2200VA,16A

APPLICABLE REQUIREMENTS

CSA-C22.2 No. 107.1-01 - General Use Power Supplies -Industrial Products

MARKINGS

See Descriptive Report.