

CERTIFICATE

Issued to:
Applicant:
American Power Conversion Holding Inc.
3F. No. 205, Sec. 3, Beixin Road,
Xindian District, New Taipei City, 231 Taiwan
R.O.C.

Manufacturer/Licensee:
Dongguan Quan Sheng Electric Co., Ltd.
Ju-Tang 2nd Industrial Park
523963 Dongguan, Guangdong, China

Product(s) : plug-in adaptors with Surge Protective Device
Trade name(s) : APC by Schneider Electric
Type(s)/model(s) : PM1W.-UK Series

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standards BS 1363-1:1995 + A4:2012; BS 1363-2:1995 + A4:2012; BS 5733:2010 + A1:2014; EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 and EN 61643-11:2012
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2025917

DEKRA hereby grants the right to use the KEMA-KEUR BS certification mark.

The KEMA-KEUR BS certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR BS certification agreement and under the conditions of the KEMA-KEUR BS certification agreement.

This certificate is issued on: 04 August 2015 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 4322701.01

DEKRA Certification B.V.



drs. G.J. Zoetbrood
Managing Director



Rosa Zhou
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

product	:	plug-in adaptors with Surge Protective Device
trade name(s)	:	APC by Schneider Electric
type(s)	:	PM1W-UK, PM1WU2-UK
rated current	:	13 A
rated voltage	:	250 V~
earthing plug part	:	with earthing-pin
earthing socket-outlet part	:	with earthing-contact
design	:	non-rewirable adaptors, non moulded-on
standard sheet plug part	:	according to BS 1363-1
standard sheet socket-outlet part	:	according to BS 1363-2
description	:	enclosure of thermoplastic material, provided with AC Surge Protective Device and optional with dual USB-Charger
markings	:	are marked on the enclosure

Product data - type PM1W-UK

design	:	provided with AC Surge Protective Device
--------	---	--

Product data - type PM1WU2-UK

design	:	provided with AC Surge Protective Device and dual output USB-Charger
--------	---	--

TESTS**Test requirements**

BS 1363-1:1995 + A4:2012
BS 1363-2:1995 + A4:2012
BS 5733:2010 + A1:2014
EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013
EN 61643-11:2012

Test result

The test results are laid down in DEKRA test file 4322701.01.

Remarks

The USB-Charger is tested as part of the plug in adaptors and the test results are laid down in DEKRA Test File 4322709.00

The Surge Protective Devices are tested as part of the plug in adaptors and the test results are laid down in DEKRA Test File 3169139.00

The products specified in this certificate comply with the above-mentioned standards solely for use in those countries where the above-mentioned standards apply.

Conclusion

The examination proved that all test requirements were met.

Tested by : A. Han 
J. Huang 
K. Zhang 
Checked by : J.C. Hendriksen 
L. Wang 

Factory location

Dongguan Quan Sheng Electric Co., Ltd.
Ju-Tang 2nd Industrial Park, 523963, Dongguan, Guangdong, China

List of components

Component	trade name	type/model	approval mark ¹⁾
AC Surge Protective Device	PT	SBA108 REV:A0 (Uc: 250V~, Uoc 6kV, Up:1.6kV, IL:13A)	*
Varistors (MOV)	EV (EnergeticTech Co.)	14S471X3	*
thermal fuse (TF1)	SET (Xiamen Set)	C2 (5A/250V~, 115 °C)	*
thermal fuse (TF2)	SET (Xiamen Set)	C1 (5A/250V~, 102 °C)	*
Capacitor (CX1)	EG (Dongguan Easy Gather)	MKP-X2 .1K 300V	ENEC10
Gas Tube	Wujin Jiangnan Discharge Tube Co., Ltd.	JN2R600	*
Dual port USB-charger	PT	SBA108 USB CHARGER.A (5V/2.4A)	*
¹⁾ * indicates a component tested as part of the product(s)			