



中国国家强制性产品认证证书

证书编号: 2004010309123237

委托人名称、地址

上海施耐德工业控制有限公司
中国上海市普陀区绥德路629号

生产者(制造商)名称、地址

Schneider Electric a. s.
Cizovska 447 - 39701 Pisek - Czech Republic

生产企业名称、地址

Schneider Electric a. s.
Cizovska 447 - 39701 Pisek - Czech Republic

产品名称和系列、规格、型号

热过载继电器

LR2K0301, LR2K0302, LR2K0303, LR2K0304, LR2K0305, LR2K0306, LR2K0307,
LR2K0308, LR2K0310, LR2K0312, LR2K0314, LR2K0316, LR2K0321, LR2K0322,
LR7K0301, LR7K0302, LR7K0303, LR7K0304, LR7K0305, LR7K0306,
LR7K0307, LR7K0308, LR7K0310, LR7K0312, LR7K0314, LR7K0316,
LR7K0321, LR7K0322; 详见附件

产品标准和技术要求

GB 14048.4-2010

上述产品符合强制性产品认证实施规则
CNCA-C03-02: 2014的要求, 特发此证。

发证日期: 2016年07月28日 有效期至: 2021年07月28日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2004年07月07日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 1367500



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2004010309123237

NAME AND ADDRESS OF THE APPLICANT

Schneider Shanghai Industrial Control Co., Ltd
629 Sui De Road, Pu Tuo District, Shanghai, P.R.C

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric a. s.
Cizovska 447 - 39701 Pisek - Czech Republic

NAME AND ADDRESS OF THE FACTORY

Schneider Electric a. s.
Cizovska 447 - 39701 Pisek - Czech Republic

NAME, MODEL AND SPECIFICATION

Thermal overload relay

LR2K0301, LR2K0302, LR2K0303, LR2K0304, LR2K0305, LR2K0306, LR2K0307,
LR2K0308, LR2K0310, LR2K0312, LR2K0314, LR2K0316, LR2K0321, LR2K0322,
LR7K0301, LR7K0302, LR7K0303, LR7K0304, LR7K0305, LR7K0306,
LR7K0307, LR7K0308, LR7K0310, LR7K0312, LR7K0314, LR7K0316,
LR7K0321, LR7K0322; see the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4 2010

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-C03-02:2014).

Date of issue: Jul.28, 2016 Date of expiry: Jul.28, 2021

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Jul.07, 2004

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

Q 1367500



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2004010309123237

纸号: 1367500

LR2K0301, LR2K0302, LR2K0303,
 LR2K0304, LR2K0305, LR2K0306,
 LR2K0307, LR2K0308, LR2K0310,
 LR2K0312, LR2K0314, LR2K0316,
 LR2K0321, LR2K0322, LR7K0301,
 LR7K0302, LR7K0303, LR7K0304,
 LR7K0305, LR7K0306, LR7K0307,
 LR7K0308, LR7K0310, LR7K0312,
 LR7K0314, LR7K0316, LR7K0321,
 LR7K0322

Ui: 690V;

Ue: 690V;

Ie: 0.11-0.16A(仅适用LR2K), 0.16-0.23A(仅适用LR2K), 0.23-0.36A(仅适用LR2K),
 0.36-0.54A(仅适用LR2K), 0.54-0.8A, 0.8-1.2A, 1.2-1.8A, 1.8-2.6A,
 2.6-3.7A, 3.7-5.5A, 5.5-8A, 8-11.5A, 10-14A, 12-16A;

脱扣等级: 10A;

极数: 3P;

配用的辅助触头(本体):

Ith: 5A;

AC-15: Ue/Ie:240V/0.75A,600V/0.3A;

DC-13:Ue/Ie:250V/0.11A;

1NO, 1NC

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 2 页

证书编号: 2004010309123237

纸号: 1367500

型号解释:

LR2	K	0301
I	II	III

I-	产品基本型号 LR2: 差动热过载继电器 (有断相保护) LR7: 不平衡负载热过载继电器 (无断相保护)																												
II-	系列描述 K: K 系列																												
III-	整定范围 <table border="1"> <tr><td>0301</td><td>0.11 - 0.16 A (仅适用 LR2K)</td></tr> <tr><td>0302</td><td>0.16 - 0.23 A (仅适用 LR2K)</td></tr> <tr><td>0303</td><td>0.23 - 0.36 A (仅适用 LR2K)</td></tr> <tr><td>0304</td><td>0.36 - 0.54 A (仅适用 LR2K)</td></tr> <tr><td>0305</td><td>0.54 - 0.8 A</td></tr> <tr><td>0306</td><td>0.8 - 1.2 A</td></tr> <tr><td>0307</td><td>1.2 - 1.8 A</td></tr> <tr><td>0308</td><td>1.8 - 2.6 A</td></tr> <tr><td>0310</td><td>2.6 - 3.7 A</td></tr> <tr><td>0312</td><td>3.7 - 5.5 A</td></tr> <tr><td>0314</td><td>5.5 - 8 A</td></tr> <tr><td>0316</td><td>8 - 11.5 A</td></tr> <tr><td>0321</td><td>10 - 14 A</td></tr> <tr><td>0322</td><td>12 - 16 A</td></tr> </table>	0301	0.11 - 0.16 A (仅适用 LR2K)	0302	0.16 - 0.23 A (仅适用 LR2K)	0303	0.23 - 0.36 A (仅适用 LR2K)	0304	0.36 - 0.54 A (仅适用 LR2K)	0305	0.54 - 0.8 A	0306	0.8 - 1.2 A	0307	1.2 - 1.8 A	0308	1.8 - 2.6 A	0310	2.6 - 3.7 A	0312	3.7 - 5.5 A	0314	5.5 - 8 A	0316	8 - 11.5 A	0321	10 - 14 A	0322	12 - 16 A
0301	0.11 - 0.16 A (仅适用 LR2K)																												
0302	0.16 - 0.23 A (仅适用 LR2K)																												
0303	0.23 - 0.36 A (仅适用 LR2K)																												
0304	0.36 - 0.54 A (仅适用 LR2K)																												
0305	0.54 - 0.8 A																												
0306	0.8 - 1.2 A																												
0307	1.2 - 1.8 A																												
0308	1.8 - 2.6 A																												
0310	2.6 - 3.7 A																												
0312	3.7 - 5.5 A																												
0314	5.5 - 8 A																												
0316	8 - 11.5 A																												
0321	10 - 14 A																												
0322	12 - 16 A																												

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

