

## Easy UPS 3S 10–40 kVA

**To whom it may concern.** This is to certify that Easy UPS 3S is manufactured in the following country(ies):

| SKU Number    | Description   | Country of Origin | Manufacturing Facility                                       |
|---------------|---|-------------------|--|
| E3SUPS10KH    | Easy UPS 3S 10 kVA 400 V 3:3 UPS for external batteries                       | China             | Schneider Electric Information Technology (Xiamen) Co., Ltd. |
| E3SUPS10KHB   | Easy UPS 3S 10 kVA 400 V 3:3 UPS for internal batteries                       |                   |  |
| E3SUPS10KHB1  | Easy UPS 3S 10 kVA 400 V 3:3 UPS with internal batteries - 15 minutes runtime | China             | Schneider Electric IT (China) Co., LTD.                      |
| E3SUPS10KHB2  | Easy UPS 3S 10 kVA 400 V 3:3 UPS with internal batteries - 40 minutes runtime |                   |  |
| E3SUPS10K3I   | Easy UPS 3S 10 kVA 400 V 3:1 UPS for external batteries                       | Philippines       | American Power Conversion Corporation (A.P.C.) B.V.          |
| E3SUPS10K3IB  | Easy UPS 3S 10 kVA 400 V 3:1 UPS for internal batteries                       |                   |  |
| E3SUPS10K3IB1 | Easy UPS 3S 10 kVA 400 V 3:1 UPS with internal batteries - 15 minutes runtime |                   |  |
| E3SUPS10K3IB2 | Easy UPS 3S 10 kVA 400 V 3:1 UPS with internal batteries - 40 minutes runtime |                   |  |
| E3SUPS15KH    | Easy UPS 3S 15 kVA 400 V 3:3 UPS for external batteries                       |                   |  |
| E3SUPS15KHB   | Easy UPS 3S 15 kVA 400 V 3:3 UPS for internal batteries                       |                   |  |
| E3SUPS15KHB1  | Easy UPS 3S 15 kVA 400 V 3:3 UPS with internal batteries - 9 minutes runtime  |                   |  |
| E3SUPS15KHB2  | Easy UPS 3S 15 kVA 400 V 3:3 UPS with internal batteries - 25 minutes runtime |                   |  |
| E3SUPS15K3I   | Easy UPS 3S 15 kVA 400 V 3:1 UPS for external batteries                       |                   |  |
| E3SUPS15K3IB  | Easy UPS 3S 15 kVA 400 V 3:1 UPS for internal batteries                       |                   |  |
| E3SUPS15K3IB1 | Easy UPS 3S 15 kVA 400 V 3:1 UPS with internal batteries - 9 minutes runtime  |                   |  |
| E3SUPS15K3IB2 | Easy UPS 3S 15 kVA 400 V 3:1 UPS with internal batteries - 25 minutes runtime |                   |  |
| E3SUPS20KH    | Easy UPS 3S 20 kVA 400 V 3:3 UPS for external batteries                       |                   |  |
| E3SUPS20KHB   | Easy UPS 3S 20 kVA 400 V 3:3 UPS for internal batteries                       |                   |  |
| E3SUPS20KHB1  | Easy UPS 3S 20 kVA 400 V 3:3 UPS with internal batteries - 15 minutes runtime |                   |  |
| E3SUPS20KHB2  | Easy UPS 3S 20 kVA 400 V 3:3 UPS with internal batteries - 30 minutes runtime |                   |  |
| E3SUPS20K3I   | Easy UPS 3S 20 kVA 400 V 3:1 UPS for external batteries                       |                   |  |

| SKU Number    | Description   | Country of Origin | Manufacturing Facility   |
|---------------|---|-------------------|--|
| E3SUPS20K3IB  | Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries                       | China             | Schneider Electric Information Technology (Xiamen) Co., Ltd.<br>Schneider Electric IT (China) Co., LTD.<br>American Power Conversion Corporation (A.P.C.) B.V. |
| E3SUPS20K3IB1 | Easy UPS 3S 20 kVA 400 V 3:1 UPS with internal batteries - 15 minutes runtime | China             |  |
| E3SUPS20K3IB2 | Easy UPS 3S 20 kVA 400 V 3:1 UPS with internal batteries - 30 minutes runtime | Philippines       |  |
| E3SUPS30KH    | Easy UPS 3S 30 kVA 400 V 3:3 UPS for external batteries                       |                   |  |
| E3SUPS30KHB   | Easy UPS 3S 30 kVA 400 V 3:3 UPS for internal batteries                       |                   |  |
| E3SUPS30KHB1  | Easy UPS 3S 30 kVA 400 V 3:3 UPS with internal batteries - 9 minutes runtime  |                   |  |
| E3SUPS30KHB2  | Easy UPS 3S 30 kVA 400 V 3:3 UPS with internal batteries - 25 minutes runtime |                   |  |
| E3SUPS30K3I   | Easy UPS 3S 30 kVA 400 V 3:1 UPS for external batteries                       |                   |  |
| E3SUPS30K3IB  | Easy UPS 3S 30 kVA 400 V 3:1 UPS for internal batteries                       |                   |  |
| E3SUPS30K3IB1 | Easy UPS 3S 30 kVA 400 V 3:1 UPS with internal batteries - 9 minutes runtime  |                   |  |
| E3SUPS30K3IB2 | Easy UPS 3S 30 kVA 400 V 3:1 UPS with internal batteries - 25 minutes runtime |                   |  |
| E3SUPS40KH    | Easy UPS 3S 40 kVA 400 V 3:3 UPS for external batteries                       |                   |  |
| E3SUPS40KHB   | Easy UPS 3S 40 kVA 400 V 3:3 UPS for internal batteries                       |                   |  |
| E3SUPS40KHB1  | Easy UPS 3S 40 kVA 400 V 3:3 UPS with internal batteries - 10 minutes runtime |                   |  |
| E3SUPS40KHB2  | Easy UPS 3S 40 kVA 400 V 3:3 UPS with internal batteries - 15 minutes runtime |                   |  |
| E3SOPT001     | Easy UPS 3S Network Card  |                   |  |
| E3SOPT002     | Easy UPS 3S Parallel Kit  |                   |  |
| E3SOPT003     | Easy UPS 3S Temperature Sensor Kit for External Battery System                |                   |  |
| E3SOPT004     | Easy UPS 3S Cold Start Kit  |                   |  |
| E3SOPT006     | Easy UPS 3S Parallel Maintenance Bypass Panel for up to 2 Units 10-40 kVA     |                   |  |
| E3SOPT007     | Easy UPS 3S Battery Breaker Box   |                   |  |
| E3SOPT008     | Easy UPS 3S Battery Breaker Kit   |                   |  |
| E3SEBC7       | Easy UPS 3S Empty Classic Battery Cabinet (700mm)                             |                   |  |
| E3SBTU        | Easy UPS 3S Standard Battery Unit   |                   |  |
| E3SBTHU       | Easy UPS 3S High Capacity Battery Unit  |                   |  |
| E3SBT4        | Easy UPS 3S Standard Battery Module   |                   |  |
| E3SBTH4       | Easy UPS 3S High Capacity Battery Module                                      |                   |  |