

No. P07208078

Order No. 89182

Applicant	Elari Oy Konalankuja 5 00390 Helsinki FINLAND
Manufacturer	Elari Oy Konalankuja 5 00390 Helsinki FINLAND
Factory	Elari Oy Konalankuja 5 00390 Helsinki FINLAND
Trade mark	Schneider Electric
Product	Photoelectrically controller switch
Model/type	APR10
Ratings	230V 50Hz
Principal characteristics	Photoelectrically controlled switch. Semiconductor switch. IP20. Operated by infrared. Flush-type. Pillar terminals. Design A. 2300W incandescent lamp. 2000W 230V halogen lamps. 2000VA fluorescent tubes, max parallel compensation 140uF, $\cos\phi=0.9$. 1150VA low voltage halogen lamps with electronic transformers (iron core). 1050VA low voltage halogen lamps with conventional transformers. 500VA energy saving lamps. 200VA single phase motors. 200VA ac electromagnetic loads like relay coils
Standard(s)	Safety std.: EN 60669-2-1:2004 EN 60669-1:1999;A1
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.

Date of issue 28 June 2007



signature

Pål Pedersen

Certification Department