

Product	Socket outlets
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison France
Factory	Merten GmbH Fritz-Kotz-Strasse 8 DE-51674 Wiehl Germany <input type="checkbox"/> See next page(s)
Ratings	16A 250V AC
Trade mark	
Model / Type Ref.	270/**
Principal characteristics	IP20, IP21, IP 44, CEE 7 / III, Flush-type socket-outlet 2P + E, screw fixing. Available with screw terminals. Screw- or claw fixing. Available with shutters. <input type="checkbox"/> See next page(s)
A sample of the product was tested and found to be in conformity with	INST NEK-IEC 60884-1:2002;am1;am2 and NEK 502:2006
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	This certificate has attachment. This certificate replaces the certificate No. P15220351 dated 15-10-2015, due to updating of attachment. <input type="checkbox"/> See next page(s)
Additional model(s)	<input type="checkbox"/> See next page(s)

Date of issue 26-11-2015



Nastaran Vadoodi

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Attachmnet to certificate No. P15220351

Socket-outlet type list:

System Basis (Thermo/Duro)

270/2744, 270/2746, 270/2742, 270/2743, 270/2704, 270/2304

System M (Thermo/Duro)

270/2371, 270/2373, 270/2376, 270/2374, 270/2300, 270/2301, 270/2309 with or without LED light module 2003, 270/2474, 270/2485, 270/2496, 270/2470, 270/2471, 270/2472, 270/2473, 270/2334 with **LED** light module 2334

System Design (Thermo/Duro)

270/2375, 270/2377, 270/2372, 270/2379 with or without **LED** light module 2003, 270/2378, 270/2306, 270/2308, 270/2478, 270/2476, 270/2477

OctoColor

270/2740, 270/2702, 270/2740

AQUADESIGN

270/2330, 270/2335

Renova

270/EAV54699

Frame types:

System Basis (Thermo+Duro)

Atelier, MI: (1 - 5 gang)

3971, 3972, 3973, 3974, 3975

System M (Thermo+Duro)

M-Smart: (1 - 5 gang)

4841, 4842, 4843, 4844, 4845

1M: (1 - 5 gang)

3891, 3892, 3893, 3894, 3895

M-Plan II: (1 - 3 gang)

4881, 5124, 4882, 5125, 4883, 5126

M-Plan: (1 - 5 gang)

4861, 4862, 4863, 4864, 4865

M-Plan Metall: (1 - 5 gang)

4751, 4752, 4753, 4754, 4755

M-Plan Echtglas: (1 - 5 gang)

4891, 4892, 4893, 4894, 4895

M-ARC: (1 - 5 gang)

4851, 4852, 4853, 4854, 4855

M-Star: (1 - 5 gang)

4871, 4872, 4873, 4874, 4875

Attachmnet to certificate No. P15220351

Atelier-M: (1 - 5 gang)
3881, 3882, 3883, 3884, 3885

System M - Elegance: (1 - 5 gang)
4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035
4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

System M - Exxact (Thermo)
Basic: (1 - 5 gang)
BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

Design: (1 - 3 gang)
BBV49558, BBV49559, BBV49561

Solid: (1 - 4 gang)
BBV49558, BBV49559, BBV49561, BBV49589

Solid Glass: (1 - 4 gang)
S1A45091, S1A45092, S1A45094, S1A45092

Combi: (1 - 5 gang)
BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

Primo: (1 - 6 gang)
BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

Gasket for all 1P44 frames: (1 - 3 gang)
BBV49557, S1A33102, S1A33103

System M - Creativ (1 - 5 gang)
4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35,

System Design (Thermo + Duro)
ARTEC, Antik, Flache: (1 - 5 gang)
4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

TRANCENT: (1 - 4 gang)
4821, 4822, 4823, 4824

OctoColor: (1 - 5 gang)
3991, 3992, 3993, 3994, 3995, 3999

AQUADESIGN: (1 - 4 gang)
4011, 4012, 4013, 4014

Renova
Glass frame: (1 - 3 gang)
BBV28342, BBV28343, BBV28344
Plasic frame: (1 - 5 gang)
101370, 101371, 101372