

Product	Light dimmer
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison Cedex France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison Cedex France
Factory	Lexel Fabrika SIA Krustpils 35a LV-1073 Riga Latvia
Ratings	230V, 50Hz, 40-400 VA
Trade mark	LK
Model / Type Ref.	IHC/SA Dimmer 400UNI
Principal characteristics	push-button / other external influences, DIN-rail/panel-type, screw type, Incandescent lamps, 230V halogen lamps and low voltage halogen lamps with electronic transformer, conventional transformer and resistive heating units 40-400 W, toroidal transformer 40-300 W and motors 40-200 W, IP20
A sample of the product was tested and found to be in conformity with	INST EN 50428:2005;A1;A2 EN 60669-1:1999;A1;A2 EN 60669-2-1:2004;A1;A12
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	
Additional model(s)	(2) See page 2

Date of issue 10-10-2017



Nastaran Vadoodi

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product	Light dimmer
Pos. No	1
Model / Type Ref.	STD400RC/RL-SAE
Trade mark (if different from page 1)	Schneider Electric
Rating	230V, 50Hz, 40-400 VA
Principal characteristics	push-button / other external influences, DIN-rail/panel-type, screw type, Incandescent lamps, 230V halogen lamps and low voltage halogen lamps with electronic transformer, conventional transformer and resistive heating units 40-400 W, toroidal transformer 40-300 W and motors 40-200 W, IP20

Product	Light dimmer
Pos. No	2
Model / Type Ref.	400GLE/I DIN
Trade mark (if different from page 1)	ELKO
Rating	230V, 50Hz, 40-400 VA
Principal characteristics	push-button / other external influences, DIN-rail/panel-type, screw type, Incandescent lamps, 230V halogen lamps and low voltage halogen lamps with electronic transformer, conventional transformer and resistive heating units 40-400 W, toroidal transformer 40-300 W and motors 40-200 W, IP20

Date of issue 10-10-2017



Nastaran Vadoodi

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532