

Product	DCL Outlet and DCL Plug
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison Cedex France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92506 Rueil-Malmaison Cedex France
Factory	(2) See page 2
Ratings	6A 250V AC
Trade mark	Schneider Electric
Model / Type Ref.	DCL plug BBV58748
Principal characteristics	Rewirable for flexible cable 3G0.5-1.0mm ² . Screw terminals. Standard sheet 1-2
A sample of the product was tested and found to be in conformity with	INST EN 61995-1:2008;A1 EN 61995-2:2009;A1
Replaces	This certificate replaces previous certificate No. P17222384, due to adding new variant.
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	
Additional model(s)	(4) See page 2

Date of issue 16-02-2018



Nastaran Vadoodi
Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product	DCL Outlet and DCL Plug
Pos. No	1
Model / Type Ref.	DCL Wall; Couplers: 15003 (Screw terminals) QGH60131 and QGH60133 (Screwless terminals); Covers: S1A88392 (Exxact design) QGH1235602 (Renova design)
Trade mark (if different from page 1)	
Rating	6A 250V AC
Principal characteristics	DCL outlet and DCL plug. Flush type, rewirable, for rigid (stranded) conductors 1.0-2.5mm ² . Mounting in wall boxes with 60mm fixing distance. Standard sheet 1-1 and 1-2
Product	DCL Outlet and DCL Plug
Pos. No	2
Model / Type Ref.	DCL Ceiling; Couplers: 15003 (Screw terminals) QGH60131 and QGH60133 (Screwless terminals); Covers: S1A88421 (inner center cover - Exxact design) S1A88397 (outer center cover - Exxact design) QGH1131302
Trade mark (if different from page 1)	
Rating	6A 250V AC
Principal characteristics	DCL outlet and DCL plug. Flush type, rewirable, for rigid (stranded) conductors 1.0-2.5mm ² . Mounting in ceiling boxes with 70mm fixing distance, a 10mm spacer can be fitted, equipped with device (hook) for hanging up to 15kg. Standard sheet
Product	DCL Outlet and DCL Plug
Pos. No	3
Model / Type Ref.	DCL spacer: WDE005103 (Exxact design)
Trade mark (if different from page 1)	
Rating	-
Principal characteristics	Frame for making additional space for DCL ceiling
Product	DCL Outlet and DCL Plug
Pos. No	4
Model / Type Ref.	DCL Wall; Coupler: QGH57336 (Screwless terminals), Covers: QGH1235702 (Exxact design)
Trade mark (if different from page 1)	
Rating	6A 250V AC
Principal characteristics	DCL Outlet. Flush type. Rewirable for rigid (stranded) conductors 1.0-2.5mm ² . Mounting in wall boxes with 60mm fixing distance. Standard sheet 1-1 and 1-2

Date of issue 16-02-2018



Nastaran Vadoodi

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Factories

Elda-Eltra Elektrotechnika S.A.
ul. Bugno 1
PL-78.400 Szczecinek
Poland

Lexel Fabrika SIA
Krustpils 35a
LV-1073 Riga
Latvia

Date of issue 16-02-2018



Nastaran Vadoodi

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532