

Product	Service pole
Applicant	Schneider Electric Sverige AB CMS Product Department, Eskilstunavägen 7 SE-611 56 Nyköping Sweden
Manufacturer	Schneider Electric Sverige AB CMS Product Department, Eskilstunavägen 7 SE-611 56 Nyköping Sweden
Factory	Schneider Electric Wibe Sweden Wibevägen 1 792 27 Mora Sweden
Ratings	16A 230 V~
Trade mark	
Model / Type Ref.	POL-M10
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. With Flush mounted components CAN/CYB and telecom components, With circular floor standing.
A sample of the product was tested and found to be in conformity with	INST EN 50085-1:2005;A1 EN 50085-2-4:2009
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	
Additional model(s)	(5) See page 2

Date of issue 25-02-2019



Jiyea Gim
Certification Department

Nemko AS
Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product	Service pole
Pos. No	1
Model / Type Ref.	POL-M20
Trade mark (if different from page 1)	
Rating	16 A 230 V~
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. With Flush mounted components CAN/CYB and telecom components, With circular floor standing.
Product	Service pole
Pos. No	2
Model / Type Ref.	POL-T10
Trade mark (if different from page 1)	
Rating	16 A 230 V~
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. For mounting between floor and ceiling.
Product	Service pole
Pos. No	3
Model / Type Ref.	POL-T20
Trade mark (if different from page 1)	
Rating	16 A 230 V~
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. For mounting between floor and ceiling.
Product	Service pole
Pos. No	4
Model / Type Ref.	POL-F10
Trade mark (if different from page 1)	
Rating	16 A 230 V~
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. With Flush mounted components CAN/CYB and telecom components. For mounting on floor.
Product	Service pole
Pos. No	5
Model / Type Ref.	POL-F20
Trade mark (if different from page 1)	
Rating	16 A 230 V~
Principal characteristics	Cl. I, IP40, Prewired Service pole with flexible supply cable H05VV-F 3x1.5 mm ² and telecom cable. With Flush mounted components CAN/CYB and telecom components. For mounting on floor.

Date of issue 25-02-2019

Jiyea Gim

Jiyea Gim

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532