


Product	Membrane
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier, P.O Box 30323 FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier, P.O Box 30323 FR 92500 Rueil-Malmaison France
Factory	ELTEC S.r.l. 7-Th Piatra Craiului St. Negoiesti, Brazi 107086 Romania
Ratings	IP67
Trade mark	 THORSMAN or
Model / Type Ref.	TET 3-5
Principal characteristics	TET 3-5 Grey EPDM or TET 3-5C black CR membrane inlet for cables with diameter 3-5 mm for 12-13 mm mounting hole and 0.5-2 mm wall thickness.
A sample of the product was tested and found to be in conformity with	INST EN 60670-1:2005;A1
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	
Additional model(s)	(13) See page 2

Date of issue 08-04-2019

Jiyea Gim

Jiyea Gim
Certification Department

Nemko AS
Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product	Membrane
Pos. No	1
Model / Type Ref.	TET 10-14
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 10-14 Grey EPDM or TET 10-14C black CR membrane inlet for cables with diameter 10-14 mm for 23-24 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	2
Model / Type Ref.	TET 20-26
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 20-26 Grey EPDM or TET 20-26C black CR membrane inlet for cables with diameter 20-26 mm for 38-39 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	3
Model / Type Ref.	TET 20-26C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 20-26 Grey EPDM or TET 20-26C black CR membrane inlet for cables with diameter 20-26 mm for 38-39 mm mounting hole and 1-4 mm wall thickness
Product	Membrane
Pos. No	4
Model / Type Ref.	TET 26-35
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 26-35 Grey EPDM or TET 26-35C black CR membrane inlet for cables with diameter 26-35 mm for 48-49 mm mounting hole and 1-4 mm wall thickness

Date of issue 08-04-2019

Jiyea Gim

Jiyea Gim

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway

TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532

Product	Membrane
Pos. No	5
Model / Type Ref.	TET 26-35C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 26-35 Grey EPDM or TET 26-35C black CR membrane inlet for cables with diameter 26-35 mm for 48-49 mm mounting hole and 1-4 mm wall thickness
Product	Membrane
Pos. No	6
Model / Type Ref.	TET 3-5C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 3-5 Grey EPDM or TET 3-5C black CR membrane inlet for cables with diameter 3-5 mm for 12-13 mm mounting hole and 0.5-2 mm wall thickness.
Product	Membrane
Pos. No	7
Model / Type Ref.	TET 5-7
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 5-7 Grey EPDM or TET 5-7C black CR membrane inlet for cables with diameter 5-7 mm for 16-17 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	8
Model / Type Ref.	TET 5-7C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 5-7 Grey EPDM or TET 5-7C black CR membrane inlet for cables with diameter 5-7 mm for 16-17 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	9
Model / Type Ref.	TET 7-10
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 7-10 Grey EPDM or TET 7-10C black CR membrane inlet for cables with diameter 7-10 mm for 19-20 mm mounting hole and 1-4 mm wall thickness

Date of issue 08-04-2019

Jiyea Gim

Jiyea Gim

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway

TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532

Product	Membrane
Pos. No	10
Model / Type Ref.	TET 7-10C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 7-10 Grey EPDM or TET 7-10C black CR membrane inlet for cables with diameter 7-10 mm for 19-20 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	11
Model / Type Ref.	TET 10-14C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 10-14 Grey EPDM or TET 10-14C black CR membrane inlet for cables with diameter 10-14 mm for 23-24 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	12
Model / Type Ref.	TET 14-20
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 14-20 Grey EPDM or TET 14-20C black CR membrane inlet for cables with diameter 14-20 mm for 29-30 mm mounting hole and 1-4 mm wall thickness.
Product	Membrane
Pos. No	13
Model / Type Ref.	TET 14-20C
Trade mark (if different from page 1)	
Rating	IP67
Principal characteristics	TET 14-20 Grey EPDM or TET 14-20C black CR membrane inlet for cables with diameter 14-20 mm for 29-30 mm mounting hole and 1-4 mm wall thickness

Date of issue 08-04-2019



Jiyea Gim

Certification Department

Nemko AS

Gaustadalléen 30, P.O. Box 73 Blindern, 0314 Oslo, Norway
TEL +47 22 96 03 30 FAX +47 22 96 05 50 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532