


Product	Electronic control units for luminaires
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Factory	Enics Eesti AS Valga mnt. 7A 61504 Elva Estonia
Ratings	400W(incandescent lamps) 400VA(electronic step-down converter for low voltage halogen lamps) 230V AC 50Hz
Trade mark	
Model / Type Ref.	SBD 1-10V
Principal characteristics	Pillar, screw type terminals, Pattern no. 1. IP20, IP44 when using specific Exxact designs. Electronic dimmer for electronic ballasts and transformers, flush mounting, fuse F6, 3AH and μ -disconnection
A sample of the product was tested and found to be in conformity with	INST EN 60669-1:1999;A1;A2 EN 60669-2-1:2004;A1;A12
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	See page 2
Additional model(s)	No additional models

Date of issue 23-01-2020



Okhyun Jeon
Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional information

Cover designs for inserts: SBD 1-10V. If the design includes frames sold separately its material is listed in column 3. All frames are from 1-5 gang.

Design	Reference Cover	Reference Frame
Trend	100949	100520
Trend Solid	100949	101543 (thermoplastic/glass/metallic)
Renova/Arezzo	101368	101370
Artic	13620	13601 (thermoplastic)
Artic Decor	13620	13806 (thermoplastic/glass/metallic)
Senso	20005157	20005048/20005050
Fashion	227010-0-1	21169.51-0:1
Riva	227010-0-1	204120-0-1
Scala	227010-0-1	21169.70-0:1
Novia	100634	100600 + 100601
Classic	227010-0-1	21169.151-0:1
Joy	267010-0-1	264100-0-1
MPLAN (System M)	5699	4861 (thermoplastic)
MPLAN II (System M)	5699	4881 (thermoplastic)
MPLAN metal (System M)	5699	4751 (metallic)
M-PLAN real glass (System M)	5699	4891 (real glass)
M-ARC (System M)	5699	4851 (thermoplastic)
M-STAR (System M)	5699	4871 (metallic)
Atelier-M (System M)	5699	3881 (thermoplastic)
1-M (System M)	5699	3891 (thermoplastic)
M-Smart (System M)	5699	4841 (thermoplastic/thermoset)
Elegance (System M)	5699	4021 (thermoplastic), 4031 (metallic), 4041 (glass), 4051 (wood)
ARTEC	5720	4811 (thermoplastic/metallic/thermoset)
Antik	5720	4831 (thermoplastic/metallic)
D-Life	NHA5193102	NHA2920502 (thermoplastic), NHA2923102 (metal), NHA2922102 (glass/stone)
Forum	13620	W450104
Duet	-	-
Wessen 59	-	-
Exxact Primo	BBV39712	BBV49557 (gasket), BBV49583 (Primo IP44)
Exxact Basic	BBV39712	BBV49557 (gasket), BBV49550 (Basic IP44)
Exxact	BBV39712	Combi BBV49575; Basic BBV49550, Primo BBV49558; Solid BBV49558, Solid Glass S1A45091, Primo BBV49583 (IP2x)
Delo (Odace)	BBV4007302	BBV4007602 + S1A2148202
Unica	2004912	6.002.—

Date of issue 23-01-2020



Okhyun Jeon

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway

TEL +47 22 96 03 30 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532