

Product	Junction box
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Sverige AB CMS Product Department, Eskilstunavägen 7 SE-611 56 Nyköping Sweden
Factory	(2) See page 2
Ratings	450V, IP30
Trade mark	
Model / Type Ref.	TB32/42
Principal characteristics	Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 32/42 with inner depth of 26 mm. Temperature range -25/+90°C.
A sample of the product was tested and found to be in conformity with	INST EN 60670-1:2005;A1 EN 60670-21:2007
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	
Additional model(s)	(3) See page 2

Date of issue 21-07-2021



Sweet Yuan

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway

TEL +47 22 96 03 30 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532

Additional model(s)

Product Junction box
Pos. No 1
Model / Type Ref. TB77/SH53
Trade mark (if different from page 1)
Rating 450V, IP30
Principal characteristics Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 77/53 with inner depth of 104 mm. Temperature range -25/+90°C.

Product Junction box
Pos. No 2
Model / Type Ref. TB50/SH26
Trade mark (if different from page 1)
Rating 450V, IP30
Principal characteristics Circular flush mounting box for accessory, for ceiling mounting with inlets for 16 and 20 mm conduits with locking spring and 4 knock-outs at the bottom for 16 and 20 mm conduits. Type TB 50/SH26 with inner depth of 44 mm. Temperature range -25/+90°C.

Product Junction box
Pos. No 3
Model / Type Ref. 60/46
Trade mark (if different from page 1)
Rating 450V, IP30
Principal characteristics Light grey or alternative Multifix Bio in white colour. Circular flush mounting box for accessory, for post mounting with inlets for 16 mm corrugated conduit. Temperature range -25/+90°C

Factories

Elda-Eltra Elektrotechnika S.A.
ul. Bugno 1
PL-78.400 Szczecinek
Poland

Minera AS
Folmovegen 52
2150 ÅRNES
Norway

Date of issue 21-07-2021



Sweet Yuan

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532