

No. P10212769

Accredited Certificate (ref. NA-PROD 001)

Order No. 154476

Additional information:

Additional parts and information for S90 and S100

Type ref. of base: S90
S100 same as S90 but with different interface between inner and outer rockers

Bases for rocker switches:		Rating	Pattern
S90/1/...		16 AX, 250 V	1
S90/1K/...		16 AX, 250 V	1
S90/1/...	with separate lamp circuit	16 AX, 250 V	1
S90/2/...		16 AX, 250 V	2
S90/2K/...		16 AX, 250 V	2
S90/3/...		10 A, 400 V	3
S90/5/...		16 AX, 250 V	5
S90/6/1/...		16 AX, 250 V	6
S90/6/1K/...		16 AX, 250 V	6
S90/7/...		16 AX, 250 V	7
S90/6+6/...		16 AX, 250 V	6+6
S90/6/2/...		10 A, 250 V	6/2
S90/2+1/...		16 AX, 250 V	2+1
S90/3x1/...		10 A, 400 V	3x1
S90/1+1+1/...		16 AX, 250 V	1+1+1

Bases for push-button switches with momentary contact:		Rating	Pattern
S90/1T /...	break or make contact	16 AX, 250 V	1
S90/1KT/...	make contact	16 AX, 250 V	1
S90/1T/...	with separate lamp circuit	16 AX, 250 V	1
S90/2T/...	make contact	16 AX, 250 V	2
S90/4T/...		16 AX, 250 V	4
S90/5T/...	break or make contact	16 AX, 250 V	5
S90/6T/...	break or make contact	16 AX, 250 V	6
S90/6KT/...	break or make contact	16 AX, 250 V	6
S90/6/2T/...	break or make contact	16 AX, 250 V	6/2
S90/6+6T/...	break or make contact	16 AX, 250 V	6+6

Date of issue 31 August 2010



signature

Hanne Yndestad

Certification Department

No. P10212769

Accredited Certificate (ref. NA-PROD 001)

Order No.

154476

Additional parts and information for S90

Schneider design range:

The bases has following additional parts:

Signal lamp: 21516 (13786)

Claws: 21518

Covering parts to bases:

Cover: 13396, 13626, 13750, 13549 special cover

Cover IP44: 13427, 13428, 13752.01 / 13752 with lens 13686
13752.01, red colour, with text "ÖLJYPOLTIN / OLJEBRÄNNARE"Cover plates: 13418, 13616
13426 fixing coverCentral plates: 13419, 13617, 20005071, 20005073, 20005075
20005062 holding plate

Central plates IP44: 13617 with lens 13686

Bottom plates: 20161 (13397), 13627, 13751

Boxes: 13626, 13429 with or without earthing terminal

Rockers: 13420 ... 13425 (13421, 13422, 13425, with or without signal lens)
13398
20005069, 20005070, 20005067, 20005063
20005066, 20005065, 20005064, 20005068Rockers IP44: 13430 ... 13435 (13431, 13432, 13435, with or without signal lens)
13610 ... 13615 (13611, 13612, 13615, with or without signal lens)
13753, 13755, 13761, 13762, 13794, with or without lensCombination frames: 24061 ... 24065 for one ... five appliances
24111 ... 24115 for one ... five appliances
24141 ... 24145 for one ... five appliances
24101 ... 24106 for one ... six appliances

Combination frames IP44: 24131 ... 24135 for one ... five appliances

Design holders: 20005050, 20005051, 20005052, 20005053, 20005054

Decorative stripes: 24140 (13600), 20005049, 20005048 design stripe

Lenses: 12878, 13392 labeling

Sealing flange IP44: AR 44, 12919, 20571 (13763)

Combining part: 22157 (13003)

Cord-anchorage 22158 (13028)

Date of issue 31 August 2010



signature

Hanne Yndestad

Certification Department

No. P10212769

Accredited Certificate (ref. NA-PROD 001)

Order No. 154476

Additional parts and information for S90

ELSO design range:

Covering parts to base: S90
IP20
With screw-type or screwless terminals

Fixing plates: 21179.1-0:3
21179.20-0:2
361660-0-2

	Base No.	Pattern	Design
Rockers:	201100-1xy	/1+1+1/	RIVA, SCALA. FASHION bruchfest
	21179.3-0:1	/6+6/, /6+6T/	FASHION, SCALA
	21174.35xy	/6+6/	RIVA, FASHION bruchfest
	21179.24xy	/1+1+1/	NOVIA
	21179.22xy	/6+6/, /6+6T/	NOVIA
	361100xy	/1+1+1/	JOY
	361660xy	/1+1+1/, /6+6/, /6+6T/	JOY
	21179.2xy	/3x1/	FASHION. SCALA. FASHION bruchfest
	21179 21xy	/3x1/	NOVIA
	371300xy xy	/3x1/ version switch, colours	JOY
Combination frames:	21169.51-.55...	1-5 way	FASHION
	21169.70-.73...	1-4 way	SCALA
	224100-224500...	1-5 way	FASHION bruchfest
	21179.51-21179.55...	1-5 way	NOVIA
	21179.50...	colour ring, 1 way	NOVIA
	20412-20452...	1-5 way	G RIVA
	264100-264500...	1-5 way	JOY
	264110...	1 way	JOY with lettering fields
264210-264310...	2-3 way, horizontal	JOY with lettering fields	
264220-264320...	2-3 way, vertical	JOY with lettering fields	

Date of issue 31 August 2010



signature

Hanne Yndestad

Certification Department

No. P10212769

Accredited Certificate (ref. NA-PROD 001)

Order No. 154476

Additional parts and information for S100

Exact design rang:

Covering parts to base	S100 IP20, IP21, IP44 With screw type or screwless terminals
Fixing plates:	BBV44522 1-2 rockers BBV47644 3 rocker
Rockers:	Pattern BBV40546 1,2,3,6,7,6/2 BBV40549 5,6+6,2+1 BBV47560,-40554 1+1+1,3x1 BBV40554 1,6,7 (with lense) BBV49116 1,6,7 (with label field)
Combination frames:	BBV49550...554 1-5 gang Basic frames BBV49583...587 1-5 gang Primo frames BBV54904...905 2x2 2x3 gang Primo frames BBV49558,-559, -561, -562, -570-589 1-4 and 1,5 gang frames with changeable design part BBV49575-578, -580 1-5 gang frame with removeable adapter
Glass frames:	S1A45091 1-1,5 gang frames S1A45092 2 gang frames, 4 gang frames S1A45094 3-gang frames
IP44 Gaskets:	BBV49557 1-gang gasket for IP44 S1A33102 2-gang gasket for IP44 S1A33103 3-gang gasket for IP44
Signal lamp:	WDE002019 Signal lamp 230V WDE002020 Signal lamp 24V
Claw kit:	WDE002395 Claw kit WDE002795 Claw kit
Impulse spring:	WDE002027 Impulse spring for push-button function

This appendix replaces previous appendix issued 26 july 2010 due to misprint page 4

Date of issue 31 August 2010



signature

Hanne Yndestad

Certification Department