



CERTIFICATE

FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2002900

Socket-outlet

Type designation: 270/***

Certificate holder: Schneider Electric Industries SAS
35 rue Joseph Monier
92500 Rueil-Malmaison
FRANCE

The product complies with the standard(s): IEC 60884-1:2002+A1+A2
SS 428 08 34:2013+R1+T1
SFS 5610:2015+A11
NEK 502:2016

Date of expiry: 22 January 2026

Additional information in Appendix

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed:


Leif Mattsson

Date: 22 January, 2021

APPENDIX:

Reference No. SE-S-2002900

Technical Data:

Type designation	270/***
Rated voltage (V)	250V~
Rated current (A)	16A
IP-Class	IP20, IP21, IP44
Standard sheet	III
Trademark	

Product information 2P+E. One-fold flush-type fixed socket-outlet. With screw terminals. Screw- or claw fixing*. Available with- or without shutters**.

*) Socket-outlets with claw fixing are not certified for use in Norway.
 **) Socket-outlets without shutters are not certified for use in Norway.

270/*** (“***” in the type designation can be any character or blank to indicate shipping destination and/or enclosure color, not related to product safety).

Socket-outlet type list:

Antivandalism: (1-gang)
270/S1B7217902

System M-Creativ
270/2300-35

System M (Thermo/Duro)
270/2371, 270/2373, 270/2376, 270/2374, 270/2300, 270/2301, 270/2309 with or without LED light module 2003, 270/2474, 270/2485, 270/2496, 270/2470, 270/2471, 270/2472, 270/2473, 270/2334 with LED light module 2334

System Design (Thermo/Duro)
270/2375, 270/2377, 270/2372, 270/2379 with or without LED light module 2003, 270/2378, 270/2306, 270/2308, 270/2478, 270/2476, 270/2477

System Design (Thermo/Metal)
270/NHA2920902, 270/NHA2922002, 270/NHA5195702

AQUADESIGN
270/2330, 270/2335

Renova
270/EAV54699

APPENDIX:

Reference No. SE-S-2002900

Frame types:

System M: (Thermo+Duro)

M-Smart: (1 - 5 gang)

4841, 4842, 4843, 4844, 4845

1M: (1 - 5 gang)

3891, 3892, 3893, 3894, 3895

M-Plan II: (1 - 3 gang)

4881, 5124, 4882, 5125, 4883, 5126

M-Plan: (1 - 5 gang)

4861, 4862, 4863, 4864, 4865

M-Plan Metall: (1 - 5 gang)

4751, 4752, 4753, 4754, 4755

M-Plan real glas: (1 - 5 gang)

4891, 4892, 4893, 4894, 4895

M-Plan real wood: (1 - 5 gang)

4051, 4052, 4053, 4054, 4055

Atelier-M: (1 - 5 gang)

3881, 3882, 3883, 3884, 3885

System M - Elegance: (1 - 5 gang)

4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035

4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

System M - Exxact: (Thermo) Basic: (1 - 5 gang)

BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

Design: (1 - 3 gang)

BBV49558, BBV49559, BBV49561

Solid: (1 - 4 gang)

BBV49558, BBV49559, BBV49561, BBV49589

APPENDIX:

Reference No. SE-S-2002900

Solid Glass: (1 - 4 gang)

S1A45091, S1A45092, S1A45094, S1A45092

Combi: (1 - 5 gang)

BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

Primo: (1 - 6 gang)

BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

Gasket for all IP44 frames: (1 - 3 gang)

BBV49557, S1A33102, S1A33103

System M – Creativ: (1 - 5 gang)

4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35

System M – M-Pure: (1 - 5 gang)

4010-36, 4020-36, 4030-36, 4040-36, 4050-36

System Design: (Thermo + Duro)

ARTEC, Antik, Fläche: (1 - 5 gang)

4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

System Design: (Thermo + metal + glas/stone)

D-Life: (1 - 5 gang)

NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702

D-Life metal: (1 - 5 gang)

NHA2923102, 2xNHA2923302, 2xNHA2923302/1xNHA2923502,
2xNHA2923302/2xNHA2923502, 2xNHA2923302/3xNHA2923502

D-Life glas/basalt: (1 - 5 gang)

NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

AQUADESIGN: (1 - 4 gang)

4011, 4012, 4013, 4014

Antivandalism: (1 - 3 gang)

4801, 4802, 4803

Renova

Glass frame: (1 - 3 gang)





BBV28342, BBV28343, BBV28344




Plastic frame: (1 - 5 gang)

101370, 101371, 101372

APPENDIX:

Reference No. SE-S-2002900

Robust Screw-Type (270/***) Socket Outlets, IK class IK09.				Robust: frame
	Insert	Center Cover	Center Cover Adapter	
Without Shutters	270/***	101363	101599	101600 (1-gang)
With Shutters		EAV54699		
				

Trend Screw-Type (270/***) Socket Outlets		
Insert	Center Cover (with Shutters)	Frames
270	NVE66783	100520 (1-gang) 100521 (2-gang) 100522 (3-gang) 100523 (4-gang) 101524 (5-gang)
		


Intertek

APPENDIX:

Reference No. SE-S-2002900

Manufacturing Sites: Merten GmbH
Fritz-Kotz-Strasse 8
51674 Wiehl-Bomig
GERMANY

This certificate is based on CB with ref. No. DE1-63493 dated 26 June 2020, issued by VDE. This certificate replaces previously issued ref. No. 1620519 dated 22 June 2017.



Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed:  **Date:** 22 January, 2021

Leif Mattsson