

  
**CERTIFICATE**  
**FOR EUROPEAN PRODUCT SAFETY**

Reference No. SE-S-2100667

## Frame for installation equipment

**Type designation:**

4811, 4812, 4813, 4814, 4815, 4819, 4831, 4832, 4833, 4834, 4835, 4838, NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702, NHA9257802. NHA2923102. 2 x NHA2923302, 2 x NHA2923302 1 x NHA2923502, 2 x NHA2923302 2 x NHA2923502, 2 x NHA2923302 3 x NHA2923502, 4801, 4802, 4803, 4011, 4012, 4013, 4014, 4881, 5124, 4882, 5125, 4883, 5126, 4861, 4862, 4863, 4864, 4865, 4888, 4751, 4752, 4753, 4754, 4755, 4758, 4891, 4892, 4893, 4894, 4895, 4878, 4041, 4042, 4043, 4044, 4045, 4048, 3881, 3882, 3883, 3884, 3885, 3888, 4841, 4842, 4843, 4844, 4845, 3891, 3892, 3893, 3894, 3895, 3898, 4021, 4022, 4023, 4024, 4025, 4028, 4031, 4032, 4033, 4034, 4035, 4038, 4041, 4042, 4043, 4044, 4045, 4048, 4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35, 4010-36, 4020-36, 4030-36, 4040-36, 4050-36, 4025-36, BBV49550, BBV49551, BBV49552, BBV49553, BBV49554, BBV49558, BBV49559, BBV49561, BBV49589, S1A45091, S1A45092, BBV49575, BBV49576, BBV49577, BBV49578, BBV49580, BBV49585, BBV49586, BBV54904, BBV54905, BBV49583, BBV49584, BBV49587, 100101, 100102, 100103, 100104, 100105, 100112, 100113, 100114, 100115, NHA5939702, NHA5939802, NHA5939902, PHA7753102, PHA7753202, PHA7753402, PHA7753602, PHA7753702, PHA7751002, PHA7751202, PHA7751502, PHA7751702, PHA7751902, S520702X, S520704X, S520706X, S520708X, S520714X, S520716X, S520516X, S520515X, S520802X, S520804X, S520806X, S520808X, S520814X, S520816X, S520902X, S520904X, S520906X, S520908X, S520914X, S520916X, GDE7616702, GDE7616802, GDE7616902, GDE7617102, GDE7617002, GDE7617202, GDE7617302, 300101-xx, 300102-xx, 300103-xx, 300104-xx, 300105-xx, 300106-xx, 300112-xx, 300113-xx, GDE9904602, GDE9904902, GDE9905002, GDE9905602, GDE9906602, GDE9906702, GDE9907502, 101552, 100519, 234100-0-2, 234200-0-1, 234300-0-1, 274100-0-1, 274200-0-1, 264100-0-1/101198, 264200-0-1/101198, 224100-0-1, 224200-0-1, 224300-0-1, 21169.51-0:1, 21169.52-0:1, 21169.53-0:1, 21169.54-0:1, 21169.55-0:1, 203160-0-1, 204120-0-1, 204220-0-1, 204320-0-1, 204420-0-1, 204520-0-1, 101370, 101371, 101372, 101364, BBV28342, 2xBBV28343, 2xBBV28343 + 1xBBV28344, BBV28345, 21179.51-0:1, 21179.52-0:1, 21179.53-0:1, NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

**APPENDIX:**

Reference No. SE-S-2100667

**Certificate holder:** Schneider Electric Industries SAS  
35 rue Joseph Monier  
92500 Rueil-Malmaison France

**The product complies with the standard(s):** EN 60669-1:2018  
SS 428 08 34:2013+R1+T1  
SFS 5610:2015+A11  
NEK 502:2016

**Date of expiry:** 10 May, 2026

**EU Directive information:** According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

Additional information in Appendix

**Certification Body:** Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

**Signed:**

  
Date: 10 May, 2021

Henrik Wikström

**Intertek**

**APPENDIX:**

Reference No. SE-S-2100667

**Technical Data:**

*Type designation*

4811, 4812, 4813, 4814, 4815, 4819, 4831, 4832, 4833, 4834, 4835, 4838, NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702, NHA9257802. NHA2923102. 2 x NHA2923302, 2 x NHA2923302 1 x NHA2923502, 2 x NHA2923302 2 x NHA2923502, 2 x NHA2923302 3 x NHA2923502, 4801, 4802, 4803, 4011, 4012, 4013, 4014, 4881, 5124, 4882, 5125, 4883, 5126, 4861, 4862, 4863, 4864, 4865, 4888, 4751, 4752, 4753, 4754, 4755, 4758, 4891, 4892, 4893, 4894, 4895, 4878, 4041, 4042, 4043, 4044, 4045, 4048, 3881, 3882, 3883, 3884, 3885, 3888, 4841, 4842, 4843, 4844, 4845, 3891, 3892, 3893, 3894, 3895, 3898, 4021, 4022, 4023, 4024, 4025, 4028, 4031, 4032, 4033, 4034, 4035, 4038, 4041, 4042, 4043, 4044, 4045, 4048, 4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35, 4010-36, 4020-36, 4030-36, 4040-36, 4050-36, 4025-36, BBV49550, BBV49551, BBV49552, BBV49553, BBV49554, BBV49558, BBV49559, BBV49561, BBV49589, S1A45091, S1A45092, BBV49575, BBV49576, BBV49577, BBV49578, BBV49580, BBV49585, BBV49586, BBV54904, BBV54905, BBV49583, BBV49584, BBV49587, 100101, 100102, 100103, 100104, 100105, 100112, 100113, 100114, 100115, NHA5939702, NHA5939802, NHA5939902, PHA7753102, PHA7753202, PHA7753402, PHA7753602, PHA7753702, PHA7751002, PHA7751202, PHA7751502, PHA7751702, PHA7751902, S520702X, S520704X, S520706X, S520708X, S520714X, S520716X, S520516X, S520515X, S520802X, S520804X, S520806X, S520808X, S520814X, S520816X, S520902X, S520904X, S520906X, S520908X, S520914X, S520916X, GDE7616702, GDE7616802, GDE7616902, GDE7617102, GDE7617002, GDE7617202, GDE7617302, 300101-xx, 300102-xx, 300103-xx, 300104-xx, 300105-xx, 300106-xx, 300112-xx, 300113-xx, GDE9904602, GDE9904902, GDE9905002, GDE9905602, GDE9906602, GDE9906702, GDE9907502, 101552, 100519, 234100-0-2, 234200-0-1, 234300-0-1, 274100-0-1, 274200-0-1, 264100-0-1/101198, 264200-0-1/101198, 224100-0-1, 224200-0-1, 224300-0-1, 21169.51-0:1, 21169.52-0:1, 21169.53-0:1, 21169.54-0:1, 21169.55-0:1, 203160-0-1, 204120-0-1, 204220-0-1, 204320-0-1, 204420-0-1, 204520-0-1, 101370, 101371, 101372, 101364, BBV28342, 2xBBV28343, 2xBBV28343 + 1xBBV28344, BBV28345, 21179.51-0:1, 21179.52-0:1, 21179.53-0:1, NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

*IP-Class*

*Trademark*

*Test Report*

*Product information*

IP20 or IP44

 or Merten

276449-TL3-1

Flush mounted frames for products according to the standards listed on page 1.

## APPENDIX:

Reference No. SE-S-2100667

<i>Included types for different designs</i>		
<i>System Design</i>	<i>Included frame types</i>	<i>Additional information</i>
ARTEC	4811, 4812, 4813, 4814, 4815, 4819	1-5 gang
Antik	4831, 4832, 4833, 4834, 4835, 4838	1-5 gang
D-Life	NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702, NHA9257802	1-5 gang
D-Life metal	NHA2923102, 2 x NHA2923302, 2 x NHA2923302 1 x NHA2923502, 2 x NHA2923302 2 x NHA2923502, 2 x NHA2923302 3 x NHA2923502	1-5 gang
D-Life glass / stone	NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702	1-5 gang
Anti vandalism	4801, 4802, 4803	1-3 gang
Aquadesign	4011, 4012, 4013, 4014	1-4 gang, with or without screwing
M-Plan II	4881, 5124, 4882, 5125, 4883, 5126	1-3 gang
M-Plan	4861, 4862, 4863, 4864, 4865, 4888	1-5 gang, with or without labelling
M-Plan Metal	4751, 4752, 4753, 4754, 4755, 4758	1-5 gang
M-Plan real glass	4891, 4892, 4893, 4894, 4895, 4878	1-5 gang
M-Plan real wood	4041, 4042, 4043, 4044, 4045, 4048	1-5 gang
Atelier-M	3881, 3882, 3883, 3884, 3885, 3888	1-5 gang
M-Smart	4841, 4842, 4843, 4844, 4845	1-5 gang, with or without labelling
1 M	3891, 3892, 3893, 3894, 3895, 3898	1-5 gang, with or without labelling
Elegance	4021, 4022, 4023, 4024, 4025, 4028, 4031, 4032, 4033, 4034, 4035, 4038, 4041, 4042, 4043, 4044, 4045, 4048	1-5 gang
M-Creativ	4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35	1-5 gang
M-Pure / M-Pure Decor	4010-36, 4020-36, 4030-36, 4040-36, 4050-36, 4025-36	1-5 gang, with or without labelling
Basic	BBV49550, BBV49551, BBV49552, BBV49553, BBV49554	1-5 gang
Design	BBV49558, BBV49559, BBV49561	1-3 gang
Solid	BBV49558, BBV49559, BBV49561, BBV49589	1-4 gang
Solid Glass	S1A45091, S1A45092	1-4 gang
Combi	BBV49575, BBV49576, BBV49577, BBV49578, BBV49580	1-5 gang
Primo	BBV49558, BBV49559, BBV49561, BBV49585, BBV49586, BBV54904, BBV54905	1-6 gang
Basic	BBV49550, BBV49551, BBV49552	1-3 gang, IP44 with gaskets BBV49557, S1A33102 or S1A33103
Design	BBV49558, BBV49559, BBV49561	1-3 gang, IP44 with gaskets BBV49557, S1A33102 or S1A33103

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.

## APPENDIX:

Reference No. SE-S-2100667

Solid	BBV49558, BBV49559, BBV49561	1-3 gang, IP44 with gaskets BBV49557, S1A33102 or S1A33103
Primo	BBV49583, BBV49584, BBV49587	1-3 gang, IP44 with gaskets BBV49557, S1A33102 or S1A33103
SEDNA	100101, 100102, 100103, 100104, 100105, 100112, 100113, 100114, 100115	1-5 gang
SEDNA	NHA5939702, NHA5939802, NHA5939902	1-3 gang, IP44
Sedna Design	PHA7753102, PHA7753202, PHA7753402, PHA7753602, PHA7753702	1-5 gang
Sedna Elements	PHA7751002, PHA7751202, PHA7751502, PHA7751702, PHA7751902	1-5 gang
Odace Styl	S520702X, S520704X, S520706X, S520708X, S520714X, S520716X, S520516X, S520515X	1-4 gang, 1 gang with key holder, 1 gang with mobile phone rack
Odace / Odace Touch	S520802X, S520804X, S520806X, S520808X, S520814X, S520816X	1-4 gang
Odace You	S520902X, S520904X, S520906X, S520908X, S520914X, S520916X	1-4 gang
Asfora EM	GDE7616702, GDE7616802, GDE7616902, GDE7617102, GDE7617002, GDE7617202, GDE7617302	1-5 gang
Asfora	300101-xx, 300102-xx, 300103-xx, 300104-xx, 300105-xx, 300106-xx, 300112-xx, 300113-xx	1-6 gang
Miluz ED	GDE9904602, GDE9904902, GDE9905002, GDE9905602, GDE9906602, GDE9906702, GDE9907502	1-4 gang, 1 gang IP44
Novia	101552, 100519	1-2 gang
Fashion	234100-0-2, 234200-0-1, 234300-0-1	1-3 gang
Joy	274100-0-1, 274200-0-1	1-2 gang
ELSO FASHION IP44	264100-0-1/101198, 264200-0-1/101198, 224100-0-1, 224200-0-1, 224300-0-1	1-3 gang, IP44
ELSO FASHION antibacterial	21169.51-0:1, 21169.52-0:1, 21169.53-0:1, 21169.54-0:1, 21169.55-0:1	1-5 gang
ELSO FASHION / ELSO RIVA / ELSO SCALA	203160-0-1	1 gang
ELSO RIVA plastic	204120-0-1, 204220-0-1, 204320-0-1, 204420-0-1, 204520-0-1	1-5 gang
ELSO RIVA	204120-0-1, 204220-0-1, 204320-0-1, 204420-0-1	1-4 gang, glass or aluminum
ELSO RENOVA plastic	101370, 101371, 101372, 101364	1-2 gang
ELSO RENOVA glass	BBV28342, 2xBBV28343, 2xBBV28343 + 1xBBV28344, BBV28345	1-3 gang
ELSO Renovierung im Elso NOVIA-Design Rahmen	21179.51-0:1, 21179.52-0:1, 21179.53-0:1	1-3 gang

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.

**APPENDIX:**

Reference No. SE-S-2100667

**Manufacturing Sites:** Merten GmbH  
Fritz-Kotz-Strasse 8  
51674 Wiehl Germany


According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

This certificate is based on VDE-certificate with ref. No. 130046 dated 15 January 2021, issued by VDE.

**Certification Body:** Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

**Signed:**



**Date:** 10 May, 2021

Henrik Wikström

Intertek