



CERTIFICATION RECORD

The company named below has been authorized by CSA International to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File No: 063938_C_000
Class No: 5311 08 POWER SUPPLIES Uninterruptible Power Systems

SUBMITTOR

4509998 American Power Conversion Corp.
85 Rangeway Rd Bldg 2
North Billerica, MA 01862
USA

FACTORIES

4509997 American Power Conversion Corp.
132 Fairgrounds Rd
West Kingston, RI 02892
USA

4552195 American Power Conversion Corp.
40 Catamore Blvd
East Providence, RI 02914
USA

4552196 American Power Conversion Corp.
2nd St. Peza
Cavite Economic Zone
Rosario Cavite,
Philippines

4552199 American Power Conversion Corp.
Lot 10, Blk 16, Phase IV, Peza
Cavite Economic Zone
Rosario Cavite,
Philippines

4641707 American Power Conversion
Lot 3 Blk 14, Phase III, PEZA
Cavite Economic Zone
Rosario Cavite,

Philippines

4655076 American Power Conversion
1600 Division Rd
West Warwick, Rhode Island 02893
USA

4656698 APC India
No. 187/3 & 188/3 Jigani Village
Jigani Hobli
Anekal Taluk
Bangalore District, 562106
India

4687446 International Precision Assemblies,
Inc.
Block 8 Lot 6 Phase II
PEZA
Rosario Cavite, 4106
Philippines

4688708 American Power Conversion Brazil
Ltda
Alameda Xingu 850 Alphaville
Alphaville-Barueri, São Paulo 06455-030
Brazil

February 20, 2006

CATEGORY PROGRAM

To the requirements of C22.2 No 107.3-03:

Uninterruptible power supplies, cord-connected, for use in controlled environments:

Model	Input	Output
J10	120V ac, 60Hz, 12A	120V ac, 47-63Hz, 1000VA, 600W, 9A
J15	120V ac, 60Hz, 12A	120V ac, 47-63Hz, 1440VA, 865W, 12A
S10	120V ac, 47-63Hz, 12A	120V ac, 47-63Hz, 1000VA, 700W, 9A
S15, RLC1080	120V ac, 47-63Hz, 12A	120V ac, 47-63Hz, 1440VA, 900W, 12A

sp