



CERTIFICATION RECORD

The company named below has been authorized by CSA International to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File No: 063938_C_000
Class No: 5311 05 POWER SUPPLIES Stand-alone

SUBMITTOR

4509998 American Power Conversion Corp.
85 Rangeway Rd Bldg 2
North Billerica, MA 01862
USA

FACTORIES

4509997 American Power Conversion Corp.
132 Fairgrounds Rd
West Kingston, RI 02892
USA

4552195 American Power Conversion Corp.
40 Catamore Blvd
East Providence, RI 02914
USA

4552196 American Power Conversion Corp.
2nd St. Peza
Cavite Economic Zone
Rosario Cavite,
Philippines

4552199 American Power Conversion Corp.
Lot 10, Blk 16, Phase IV, Peza
Cavite Economic Zone
Rosario Cavite,
Philippines

4641707 American Power Conversion
Lot 3 Blk 14, Phase III, PEZA
Cavite Economic Zone
Rosario Cavite,

SUA1000IX38	220-240V, 60Hz, 7A	220-240V, 60Hz, 670W, 1000VA, 4.5A
SUA1500IX38	220-240V, 60Hz, 7A	220-240V, 60Hz, 980W, 1500VA, 6.8A

- UPS hot swap-out box, Model AP019, cord connected, input/output, rated 120V, 50/60Hz, 12A. Certified as an accessory for use with the manufacturer's line of Certified UPS's.
- Line isolation transformer assembly, cord connected, Model AP017, input rated 115V ac, 11A; output rated 115V ac, 11A, 1250VA, 50/60Hz max.
- Line regulators Models Line-R600 and Line-R1250, input rated 120V, 50/60Hz, 7/12A, output rated 120V, 50/60Hz, 600/1250VA respectively.
- External battery packs, Models SU24XLBP, 1 x 114, SU48XLBP, 1 x 114 and SU48BP, SU24RMXLBP2U, SU48RMXLBP, rated 24V dc, 48V dc and 48V dc respectively.
- Line regulators: Model H10, input rated 120V, 47-63Hz, 12A; output rated 120V, 47-63Hz, 1000VA and Model H15 or RLC1040, input rated 120V, 47-63Hz, 12A; output rated 120V, 47-63Hz, 1440VA.
- UPS Component Model SYPM rated 200-240V ac, 50-60Hz, 20A input; 200/220/230/240V ac, 50-60Hz, 4kVA, 2.8kW, 20A output. ACCESSORIES FOR USE WITH 'MATRIX' SERIES UPS UNITS:
- Series MXA100 to MXA199, miscellaneous extension cord sets, power distribution units, 240V ac, 30A max, 60Hz, 3 or 4 wire.
- Hard-wire kit accessory, Models MXZ001 and MXA002.
- Battery Cabinets Models SYXR4, SYXR4J-BM and SYXR12 rated 120Vdc, 7.0AH per module; Accessories for use with "MATRIX SERIES" UPS units.

Model	Input	Output
BF400, BF400C	120V, 60Hz, 10A	Surge: 120V, 60Hz, 10A UPS 120V, 60Hz, 3A, 250W, 400VA, 10A total outputs.
BF350, BF350BB, BF350U	120V, 60Hz, 10A	Surge: 120V, 60Hz, 10A UPS: 120V, 60Hz, 225W, 350VA.
BF500, BF500BB, BF500U	120V, 60Hz, 10A	Surge: 120V, 60Hz, 10A UPS: 120V, 60Hz, 325W, 500VA.
SU5000, SU5000R5TX168, SU50000RMT5U, SU5000R5TBX120, SU50000R5TBX135, SU5000R5TBX114 and DL50000RMT5U	208V, 60Hz, 24A	208V, 60Hz, 5000VA, 3750W
SU5000RMXL5U	208V, 50/60Hz, 24A, 1Ph	200V, 50/60Hz, 22A, 5000VA, 4000W
Power Stack 250, PS 250	120V, 60Hz, 7A	120V, 60Hz, 165W
Power Stack 450, PS 450	120V, 60Hz, 7A	120V, 60Hz, 280W
Bay Stack 450	120V, 60Hz, 7A	120V, 60Hz, 280W
CNB700X	120V, 60Hz, 12A	Surge: 120V, 60Hz, 12A 120V, 60Hz, 410W, 700VA
CNB900X	120V, 60Hz, 12A	Surge: 120V, 60Hz, 12A 120V, 60Hz, 500W, 900VA
SUA1500, SUA1500US, DLA	120V, 50/60Hz, 12A	120V, 50/60Hz, 980W, 1400VA