



Ref. Certif. No.

DK-61641-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product

Class I LED luminaire for fixed installation

Name and address of the applicant

SCHNEIDER ELECTRIC ESPANA S A
C/LLOBREGAT 15
MOLINS DE REI, 08750 Spain

Name and address of the manufacturer

SCHNEIDER ELECTRIC ESPANA S A
C/LLOBREGAT 15
MOLINS DE REI, 08750 Spain

Name and address of the factory

NINGBO QIYUANLIGHTING TECH CO. LTD
NO.238 HENANGU
CHAIQIAO
BEILUN
NINGBO, 315800 ZHEJIANG China

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

Additional Information on page 2
120-230 V~ 50/60 Hz 10 W Class I IP20

Trademark (if any)



Type of Manufacturer's Testing Laboratories used

Model / Type Ref.

NSYLAMLDS
See Page 2

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1(ed.8), IEC 60598-2-1(ed.1), IEC 60598-2-1(ed.1);am1

As shown in the Test Report Ref. No. which forms part of this Certificate

4787675292-1 issued on 2017-02-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-03-29

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-61641-UL

Model details:

Variants:

The main model:

Type ref.	Ratings	Details
NSYLAMLDS	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet SHUKO

extends the following models:

Type ref.	Ratings	Details
NSYLAMLDF	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet UTE
NSYLAMLDB	120-230 V~ 50/60 Hz 10 W Class I IP20	With auxiliary socket outlet UK

Additional Information:

Also investigated to EN 60598-1:2015 and EN 60598-2-1:1989
National Differences specified in the CB Test Report

Additional information (if necessary)

Information complémentaire (si nécessaire)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-03-29

Signature: 
Jan-Erik Storgaard