

LXM28 & BCH2 UL Certification

To check certification status for LXM28 and BCH2 please go to UL certification directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.html>

LXM28 (E189729): cULus Listing NMMS/7

<http://database.ul.com> UL 508C

<http://database.ul.com> CSA C22.2 No. 274

Power conversion equipment Model(s) LXM28AU01M3X, LXM28AU02M3X, LXM28AU04M3X, LXM28AU07M3X, LXM28AU10M3X, LXM28AU15M3X, LXM28AU20M3X, LXM28AU30M3X, LXM28AU45M3X, LXM28AU5M3X

BCH2 (E471744): cURus Recognized Component PRHZ2/8

<http://database.ul.com> UL 1004-1

<http://database.ul.com> CSA C22.2 No. 100

Model No.	Output	Hz/DC	Volts	FL Amps	Service Factor	SF Amps	Poles	Number of Speeds	RPM	Capacitor Rating	Phases	Ins Class	Duty	Prot. Type	Rated Ambient (°C)
(click on a model number to see complete product details)															
BCH2HF0730CA5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0730CF5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0731CA5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0731CF5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0732CA5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0732CF5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0733CA5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40
BCH2HF0733CF5C	750W, 2.39Nm	67-400	230	4.01/4.29	-	-	8	Var	1000-6000	-	3	F	Cont	-	40

Schneider Electric Automation GmbH

Schneiderplatz 1
97828 Marktheidenfeld
Tel.: +49 9391 606-0
Fax: +49 9391 606-4000
<http://www.schneider-electric.com>
SE-Entity Code (HFM): DE5300

Sitz der Gesellschaft: Marktheidenfeld
Amtsgericht Würzburg: HRB 10733
Geschäftsführer:
Thomas Martis, Ottmar Himmelsbach
UST-IdNr.: DE 261 529 553
St.-Nr.: 231/118/40288 Finanzamt Loehr am Main