



Ref. Certif. No.

US-35456-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Accessory, Automatic Transfer Switch - Single Phase for use in certified ITE
Name and address of the applicant	SCHNEIDER ELECTRIC IT CORPORATION 70 MECHANIC ST FOXBORO, MA 02035 UNITED STATES
Name and address of the manufacturer	SCHNEIDER ELECTRIC IT CORPORATION 70 MECHANIC ST FOXBORO, MA 02035 UNITED STATES
Name and address of the factory	DANAM PHILIPPINES INC BLK 15, PHASE 3, LOT 1-A PEZA ROSARIO 4106 CAVITE PHILIPPINES
Note: When more than one factory, please report on page 2	<input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Pages 2 through 4 for Ratings <input checked="" type="checkbox"/> Additional Information on page 2-4
Trademark (if any)	APC by Schneider Electric 
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	AP4421, AP4422, AP4423, AP4424, AP4425, AP4430, AP4431, AP4432, AP4433, AP4434, AP4450, AP4452, AP4452J, AP4453 <input type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include administrative modifications. <input checked="" type="checkbox"/> Additional Information on page 4
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E177299-A6009-CB-1 issued on 2021-04-15

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-04-15
Original Issue Date: 2020-03-19

Signature:
Jolanta M. Wroblewska



Ref. Certif. No.

US-35456-A1-UL

Ratings:

AP4421:
230V, 10A, 50/60Hz
10A PER BANK 10A MAX

AP4422:
230V, 16A, 50/60Hz
16A OUTPUT MAX

AP4423:
INPUT:
220-230 VAC, 16A, 50/60Hz
UL OUTPUT:
230 VAC
10A PER C13 BANK 16A MAX
16A MAX PER C19
KOREA OUTPUT
220 VAC
10A PER C13 BANK 16A MAX
16A MAX C19

AP4424:
INPUT:
220-230 VAC, 32A, 50/60Hz,
UL OUTPUT:
230 VAC
10A PER C13 BANK 16A MAX
16A MAX C19
KOREA OUTPUT:
220 VAC
10A PER C13 BANK 16A MAX
16A MAX C19

AP4425:
230 VAC, 32A, 50/60Hz

AP4430:
UL INPUT:
208 VAC. 16A, 50/60Hz
OUTPUT:
208 VAC 16A, 50/60Hz
JAPAN
INPUT:
200 VAC, 20A, 50/60Hz
OUTPUT:
200 VAC, 20A, 50/60Hz

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Signature:

Jolanta M. Wroblewska

Date: 2021-04-15

Original Issue Date: 2020-03-19



Ref. Certif. No.

US-35456-A1-UL

Ratings:

AP4431:
INPUT:
208 VAC. 1PH 24A, 50/60Hz,
OUTPUT:
208 VAC. 1PH 24A, 50/60 Hz

AP4432:
UL INPUT:
208 VAC, 24A, 50/60Hz
OUTPUT:
208 VAC, 20A MAX PER BANK
JAPAN
INPUT:
200 VAC, 30A, 50/60Hz
OUTPUT:
200 VAC, 20A MAX PER BANK

AP4433:
INPUT:
208 VAC. 12A, 50/60Hz
OUTPUT:
208 VAC. 10A PER OUTLET 50/60Hz
10A PER C13 BANK 12A MAX

AP4434:
INPUT:
208 VAC. 16A, 50/60Hz
OUTPUT:
208 VAC. 16A 50/60 Hz
12A MAX PER C13 BANK


AP4450:
UL INPUT:
120 VAC. 12A, 50/60 Hz
OUTPUT:
120 VAC.
12A PER OUTLET 50/60 Hz
JAPAN
INPUT:
100 VAC. 15A, 50/60Hz
OUTPUT:
100 VAC. 15A PER OUTLET, 50/60Hz

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Signature: 
Jolanta M. Wroblewska

Date: 2021-04-15
Original Issue Date: 2020-03-19



Ref. Certif. No.

US-35456-A1-UL

Ratings:

AP4452:

INPUT:

120 VAC. 16A, 50/60Hz

OUTPUT:

120 VAC. 16A PER OUTLET 50/60Hz

AP4452J:

INPUT:

100 VAC. 20A, 50/60Hz

OUTPUT:

100 VAC. 15A PER OUTLET 50/60Hz

AP4453:

INPUT:

120 VAC. 24A, 50/60Hz

OUTPUT:

120 VAC. 16A MAX PER BANK

Additionally evaluated to:

EN 62368-1:2014/A11:2017; National Differences specified in the CB Test Report.

Summary of Modifications:

The original report was modified to include the following changes/additions:

Amendment 1 (Administrative):

- Updated Applicant/Manufacturer company name/address.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Signature:

Jolanta M. Wroblewska

Date: 2021-04-15

Original Issue Date: 2020-03-19