



Stock your combination

Stock the most in-demand Square D™ NEMA Combination Starters and be equipped to immediately sell more starters faster and easier than ever before.

By picking your combination, you'll have starters with these features in stock:

- Long-lasting, energy-efficient Red-ON and/or Green-OFF LED pilot lights
- Specially designed, pliable "foam-in-place" cabinet seals
- Available with electronic Motor Circuit Protector (MCP) circuit breakers or fusible/non-fusible disconnect switch
- NEMA® Type 1, 12/3R enclosure
- HOA selector switch
- Up to two Normally Open (N.O.) and two Normally Closed (N.C.) aux contacts
- 120 V separate control voltage*
- Separate control voltage interlock

**By stocking 9070TF100D1 (control power transformer) customer modifications can be made to accommodate 240/120 and 480/120 CPT installations. The 9070TF100D3 will accommodate 208/120 CPT installations.*

Class H, K fuse clips are standard. For class R fuse clip applications, use RfKxx fuse clip kits.



schneider-electric.us/SquareD

Life Is On

SQUARE D™
by Schneider Electric

Disconnect Switch Combination Starters

If your customer needs:						Pick from these starters:
NEMA Size	Fuse Clip Size	Voltage (VAC)	Horsepower	Overload Relay	Current Range	Combination Starters with Melting Alloy
0 or 1	30 A	208 or 240	3 to 5	Melting Alloy	n/a	8538SCASP1
1	60 A	208 or 240	5 to 7.5	Melting Alloy	n/a	8538SCASP2
0 or 1	30 A	480 or 600	5 to 10	Melting Alloy	n/a	8538SCASP3
1 or 2	60 A	208 or 240	7.5 to 10 (208), 7.5 to 15 (240)	Melting Alloy	n/a	8538SDASP1
1 or 2	30 A	480 or 600	10 to 15	Melting Alloy	n/a	8538SDASP2
2	60 A	480 or 600	15 to 25	Melting Alloy	n/a	8538SDASP3
0 or 1	30 A	208 or 240	0.75 to 2	Motor Logic™	3-9 FLA	8538SCASP4
1	60 A	208 or 240	3 to 7.5	Motor Logic	9-27 FLA	8538SCASP5
0 or 1	30 A	480 or 600	5 to 10	Motor Logic	6-18 FLA	8538SCASP6
1 or 2	60 A	208 or 240	5 to 10 (208), 5 to 15 (240)	Motor Logic	15-45 FLA	8538SDASP4
1 or 2	30 A	480 or 600	7.5 to 15	Motor Logic	9-27 FLA	8538SDASP5
2	60 A	480 or 600	15 to 25	Motor Logic	15-45 FLA	8538SDASP6

MCP Circuit Breaker Combination Starters*

If your customer needs:						Pick from these starters:
NEMA Size	Breaker Size	Voltage (VAC)	Horsepower	Overload Relay	Current Range	Motor Logic Solid State Starters
1	30 A	240 or 480	0.25 to 7.5 (240), 0.25 to 10 (480)	Melting Alloy	n/a	8539SCASP3
2	30 A	240 or 480	1.5 to 7.5 (240), 5 to 15 (480)	Melting Alloy	n/a	8539SDASP2
2	50 A	240 or 480	7.5 to 10 (240), 15 to 25 (480)	Melting Alloy	n/a	8539SDASP3
1	30 A	240 or 480	0.75 to 2 (240), 1.5 to 5 (480)	Motor Logic	3-9 FLA	8539SCASP6
2	30 A	240 or 480	3 to 7.5 (240), 7.5 to 15 (480)	Motor Logic	9-27 FLA	8539SDASP5
2	50 A	240 or 480	5 to 10 (240), 15 to 25 (480)	Motor Logic	15-45 FLA	8539SDASP6

* Horsepower ratings also available at 208 and 600 VAC

schneider-electric.us/SquareD

Life Is On



Schneider Electric USA

1415 S. Roselle Road, Palatine, IL 60067
 Tel: 847-397-2600
 Fax: 847-925-7500
www.schneider-electric.com

Document Number: 8500HO1003R04/18

©2018 Schneider Electric. All Rights Reserved. Schneider Electric, Square D, and Motor Logic are trademarks owned by Schneider Electric Industries SAS or its affiliated companies. All other trademarks are property of their respective owners.

998-1149809_US_A