









Choice guide

Mini-trunking for wiring device adaption

Mini-trunking Ultra for wiring device adaption





Mini-trunking for wiring device adaption		Internal corner	External corner	Bend 90°	T-piece	Joint cover piece
With one compartment	Ref. No	Ref. No.	Ref. No.	Ref. No.	Ref. No.	Ref. No.
 21x12 ETK21012	ETK21012	ETK20520	ETK20530	ETK20540	ETK20550	ETK20570
	21x12 Self-adhesive ETK21912					
 32x17 ETK32017	ETK32017	ETK32020	ETK32030	ETK32040	ETK32050	ETK32070
	32x17 Self-adhesive ETK32917					
With two compartments						
 40x17 ETK40017	ETK40017	ETK40020	ETK40030	ETK40040	ETK40050	ETK40070
With three compartments						
 60x21 ETK60021	ETK60021	ETK60020	ETK60030	ETK60040	ETK60050	ETK60070
	74x21 ETK74021					

 Stop end	 Cable retainer	 Branching piece	 Installation box kits for wiring devices
Ref. No.	Ref. No.	Ref. No	
ETK20560	ETK20571	for 21x12-60x21 ETK60022 for 21x12-74x21 ETK74022	Installation box kits for 1-3 module wiring devices, see page 18-19
ETK32060	ETK32071	for 32x17-60x21 ETK60032 for 32x17-74x21 ETK74032	
ETK40060	ETK40071	for 40x17-60x21 ETK60041 for 40x17-74x21 ETK74041	
ETK60060	ETK60071		
ETK74060	ETK74071		




Range

Mini-trunking for wiring device adaption


Mini-trunking Ultra for wiring device adaptation

Type	Colour	Dimensions A/B/C (mm)	Qty per package	EAN code	Ref. No.		
Mini-trunking with one compartment							
One-compartment mini-trunking made up by a base profile with pre-punched mounting holes on every 23 rd cm and a snap-fit front cover. Available with and without self-adhesive fixing tape. Suitable for power and low voltage cables. Supplied in 2 m lengths. Material: PVC.							
P126545		Mini-trunking 21x12	White RAL 9010	21/12/2000	128 m	8698150210121	ETK21012
		Mini-trunking 21x12 self-adhesive	White RAL 9010	21/12/2000	128 m	8698150219124	ETK21912
P126546		Mini-trunking 32x17	White RAL 9010	32/17/2000	60 m	8698150320172	ETK32017
		Mini-trunking 32x17 self-adhesive	White RAL 9010	32/17/2000	60 m	8698150329175	ETK32917
Mini-trunking with two compartments							
Two-compartment mini-trunking made up by a base profile with pre-punched mounting holes on every 23 rd cm and a snap-fit front cover. The compartments are separated by an integrated partition wall. Suitable for power and low voltage cables. Supplied in 2 m lengths. Material: PVC.							
P126215		Mini-trunking 40x17	White RAL 9010	40/17/2000	60 m	8698150400171	ETK40017
Mini-trunking with three compartments							
Three-compartment mini-trunking made up by a base profile with pre-punched mounting holes on every 23 rd cm and a snap-fit front cover. The compartments are separated by integrated partition walls. Suitable for power and low voltage cables. Supplied in 2 m lengths. Material: PVC.							
P126216		Mini-trunking 60x21	White RAL 9010	60/21/2000	40 m	8698150600212	ETK60021
		Mini-trunking 74x21	White RAL 9010	74/21/2000	24 m	8698150740215	ETK74021

Accessories Mini-trunking Ultra for wiring device adaptation

Internal corner, adjustable							
Internal corner to be snapped onto the mini-trunking base. Adjustability: $\pm 5^\circ$. Material: ABS.							
P126207		Internal corner 21x12, adjustable	White RAL 9010	23/41.5/41.5	20	8698150205202	ETK20520
		Internal corner 32x17, adjustable	White RAL 9010	20/55/55	20	8698150320202	ETK32020
		Internal corner 40x17, adjustable	White RAL 9010	47/60/60	20	8698150400201	ETK40020
		Internal corner 60x21, adjustable,	White RAL 9010	65/46/47	10	8698150600205	ETK60020
		Internal corner 74x21, adjustable	White RAL 9010	79/47/48	10	8698150740208	ETK74020
External corner, adjustable							
External corner to be snapped onto the mini-trunking base. Adjustability: $\pm 5^\circ$. Material: ABS.							
P126208		External corner 21x12, adjustable	White RAL 9010	22/40.5/40.5	20	8698150205301	ETK20530
		External corner 32x17, adjustable	White RAL 9010	20/55/55.5	20	8698150320301	ETK32030
		External corner 40x17, adjustable	White RAL 9010	46.5/41/44	20	8698150400300	ETK40030
		External corner 60x21, adjustable	White RAL 9010	65/46/46	10	8698150600304	ETK60030
		External corner 74x21, adjustable	White RAL 9010	78.5/48/49	10	8698150740307	ETK74030
Bend, 90°							
90 degree bend to be used in junctions between horizontal and vertical applications. To be snapped onto the mini-trunking base. Material: ABS.							
P126209		Bend 90° 21x12	White RAL 9010	14/35/35	10	8698150205400	ETK20540
		Bend 90° 32x17	White RAL 9010	19/55/55	10	8698150320400	ETK32040
		Bend 90° 40x17	White RAL 9010	16/66/66	10	8698150400409	ETK40040
		Bend 90° 60x21	White RAL 9010	21/92/92	10	8698150600403	ETK60040
		Bend 90° 74x21	White RAL 9010	23/104/103	10	8698150740406	ETK74040








Accessories Mini-trunking Ultra for wiring device adaptation

Type	Colour	Dimensions A/B/C (mm)		Qty per package	EAN code	Ref. No.
T-piece						
T-piece to be used in T-junctions between mini-trunking of the same size. To be snapped onto the mini-trunking base. Material: ABS.						
T-Piece 21x12	White RAL 9010	14/35/45		10	8698150205509	ETK20550
T-Piece 32x17	White RAL 9010	19/55/76		10	8698150320509	ETK32050
T-Piece 40x17	White RAL 9010	16/66/92		10	8698150400508	ETK40050
T-Piece 60x21	White RAL 9010	23/85/115		10	8698150600502	ETK60050
T-Piece 74x21	White RAL 9010	23/104/125		10	8698150740505	ETK74050
Joint cover piece						
Joint cover piece to cover joints between mini-trunking covers. To be snapped onto the mini-trunking base. Material: ABS.						
Joint cover piece 21x12	White RAL 9010	23/14/15		20	8698150205707	ETK20570
Joint cover piece 32x17	White RAL 9010	35/20/16		20	8698150320707	ETK32070
Joint cover piece 40x17	White RAL 9010	41/21/16		20	8698150400706	ETK40070
Joint cover piece 60x21	White RAL 9010	62/23/16		20	8698150600700	ETK60070
Joint cover piece 74x21	White RAL 9010	78/23/26		20	8698150740703	ETK74070
Stop end						
Stop end to be snapped onto the end of the mini-trunking base. Material: ABS.						
Stop end 21x12	White RAL 9010	23/13/7		20	8698150205608	ETK20560
Stop end 32x17	White RAL 9010	33.5/19/8		20	8698150320608	ETK32060
Stop end 40x17	White RAL 9010	42/18/8.5		20	8698150400607	ETK40060
Stop end 60x21	White RAL 9010	65/24/10		20	8698150600601	ETK60060
Stop end 74x21	White RAL 9010	78/23/10		20	8698150740604	ETK74060
Cable retainer						
Cable retainer to be snapped inside the mini-trunking base to keep cables in place during the installation phase. Material: ABS.						
Cable retainer 21x12	White RAL 9010	3.5/15/26		20	8698150205714	ETK20571
Cable retainer 32x17	White RAL 9010	3.5/25/27		20	8698150320714	ETK32071
Cable retainer 40x17	White RAL 9010	3.5/33/27		20	8698150400713	ETK40071
Cable retainer 60x21	White RAL 9010	4.5/52.5/32		20	8698150600717	ETK60071
Cable retainer 74x21	White RAL 9010	3.5/67/39.5		20	8698150740710	ETK74071
Branching piece						
Branching piece to be used in T-junctions between mini-trunking of different sizes. Material: ABS.						
Branching piece for 21x12 – 60x21	White RAL 9010	86/23/105		5	8698150600229	ETK60022
Branching piece for 21x12 – 74x21	White RAL 9010	101/23/104		5	8698150740222	ETK74022
Branching piece for 32x17 – 60x21	White RAL 9010	86/23/105		5	8698150600328	ETK60032
Branching piece for 32x17 – 74x21	White RAL 9010	101/23/104		5	8698150740321	ETK74032
Branching piece for 40x17 – 60x21	White RAL 9010	86/23/105		5	8698150600410	ETK60041
Branching piece for 40x17 – 74x21	White RAL 9010	101/23/104		5	8698150740413	ETK74041
Universal installation box kit						
Installation box kit including installation box, adaptor and fixing screws. Suitable for c/c 60 mm wiring devices. Material: ABS.						
Universal installation box kit, single	White RAL 9010	40/92/86		5	8698150205806	ETK20580
Universal installation box kit, double	White RAL 9010	40/92/156		5	8698150205967	ETK20596

Range

Mini-trunking for wiring device adaption

Accessories Mini-trunking Ultra for wiring device adaptation

Type	Colour	Dimensions A/B/C (mm)		Qty per package	EAN code	Ref. No.
Installation box kit						
Installation box kit including installation box, adaptor and fixing screws. Suitable for 45x45 module wiring devices. Material: ABS.						
P128218 	White RAL 9010	50/86/96		4	8698150205981	ETK20598
P128219 	White RAL 9010	50/92/114		5	8698150206803	ETK20680
P128217 	White RAL 9010	50/90.5/156		5	8698150205974	ETK20597
Socket outlets, Ultra						
Power socket outlet for 45x45 module earthed plug, with pin or side-earth and child protection. 250V 16A. Material: PC/ABS.						
P127841 	Red White	45/41/45		10	8690495056471 3606480517709	ETK21046E ETK21046EW
P127842 	Red White	45/41/45		10	3606480517693 8690495056488	ETK21045ER ETK21045E
Socket outlet bridge						
Socket outlet bridge providing electrical connection between two socket outlets without wiring. Material: PA6 with 20% fibre glass.						
P141289 	Grey RAL 7035	7/25/70		15	8690495056464	ETK214546