



HHH7365220001B

	G	I	E max	F max
NSYZM253	180 mm (7.08 in)	285 mm (11.22 in)	255 mm (10.04 in)	250 mm (9.84 in)
NSYZM263	180 mm (7.08 in)	385 mm (15.15 in)	355 mm (13.97 in)	250 mm (9.84 in)
NSYZM283	230 mm (9.05 in)	601 mm (23.66 in)	570 mm (22.44 in)	300 mm (11.81 in)



