

MOUNTING INSTRUCTION

Please refer to the following diagram for proper installation.



Remarks: For surround mounting, align the clip locks on the faceplate and press firm on the surround. Complete engagement of the clip locks is indicated by a clear "click" sound.





APPLICATION GUIDE Full-Flat Universal Dimmer

CAT. NO. E8431EPD4 E8432EPD3



Thank you for choosing Schneider Electric ZENcelo Full-Flat Universal Dimmer. To ensure proper application of our product, please read through the following information before installation and use

This application guide applies to the following product.

ýw)	Cat.no. E8431EPD4	Description 1 Gang 350VA 50Hz Full-Flat Universal Dimmer with LED
ý co	E8432EPD3	2 Gang 300VA 50Hz Full-Flat Universal Dimmer with LED

SPECIFICATIONS

Voltage :220-240V. 50Hz

Dimension

Load Rating :25-350VA (1 Gang), 25-300VA per gang (2 Gang) Load Type

:Incandescent, LV halogen with iron core transformer*

and electronic transformer

·87mm x 87mm

Mounting Centre :60.3mm (wall box with 35mm depth or above)


:IEC60669-2-1. C€ EMC Compliance

* Iron core transformer which is compatible to electronic dimmer must be used.

OPERATIONS

- 1. Short Press to toggle between off and last adjusted memoried light level* (the initial light level is full brightness at power up from mains)
- 2. When the load is off, double click to turn on the lamp to full brightness regardless the previous memorized light level.
- 3. Long press (press and hold) will perform cycle dimming or ramp up from minimum brightness when the load is off.
- * The memorized minimum light level will be a little bit brighter than the minimum adjustable light level.

WIRING DIAGRAMS



IMPORTANT NOTES

ZENcelo E8432EPD3 2 Gang Dimmer Application: when used in ambient temperatures greater than 25°C, the dimmer must be de-rated according to the following graph.

