



	G	I	E max	F max
NSYZZ253G	160 mm (6.30 in)	440 mm (17.32 in)	390 mm (13.38 in)	240 mm (9.45 in)
NSYZZ273G	160 mm (6.30 in)	690 mm (27.16 in)	640 mm (25.19 in)	240 mm (9.45 in)
NSYZZ2103G	160 mm (6.30 in)	940 mm (37 in)	890 mm (35.04 in)	240 mm (9.45 in)
NSYZZ2123G	160 mm (6.30 in)	1190 mm (46.85 in)	1140 mm (44.88 in)	240 mm (9.45 in)
NSYZZ254G	260 mm (10.23 in)	440 mm (17.32 in)	390 mm (13.38 in)	340 mm (13.38 in)
NSYZZ274G	260 mm (10.23 in)	690 mm (27.16 in)	640 mm (25.19 in)	340 mm (13.38 in)
NSYZZ2104G	260 mm (10.23 in)	940 mm (37 in)	890 mm (35.04 in)	340 mm (13.38 in)
NSYZZ2124G	260 mm (10.23 in)	1190 mm (46.85 in)	1140 mm (44.88 in)	340 mm (13.38 in)
NSYZZ276G	460 mm (18.11 in)	690 mm (27.16 in)	640 mm (25.19 in)	540 mm (21.25 in)
NSYZZ2126G	460 mm (18.11 in)	1190 mm (46.85 in)	1140 mm (44.88 in)	540 mm (21.25 in)