



	G	I	E max	F max
NSYZA253	195 mm (7.67 in)	380 mm (14.96 in)	340 mm (13.38 in)	200 mm (7.87 in)
NSYZA273	195 mm (7.67 in)	630 mm (24.80 in)	590 mm (23.22 in)	200 mm (7.87 in)
NSYZA2103	195 mm (7.67 in)	880 mm (34.64 in)	840 mm (33.07 in)	200 mm (7.87 in)
NSYZA2123	195 mm (7.67 in)	1130 mm (44.48 in)	1090 mm (42.91 in)	200 mm (7.87 in)
NSYZA254	295 mm (11.61 in)	380 mm (14.96 in)	340 mm (13.38 in)	300 mm (11.81 in)
NSYZA274	295 mm (11.61 in)	630 mm (24.80 in)	590 mm (23.22 in)	300 mm (11.81 in)
NSYZA2104	295 mm (11.61 in)	880 mm (34.64 in)	840 mm (33.07 in)	300 mm (11.81 in)
NSYZA2124	295 mm (11.61 in)	1130 mm (44.48 in)	1090 mm (42.91 in)	300 mm (11.81 in)