



Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Number of 18 mm modules per row	12
Number of horizontal rows	1
Provided equipment	(1) marking kit (1) insulating plug
Type of front cover	Reversible
Width	283 Mm
Height	185 Mm
Depth	94 Mm

Complementary

Enclosure mounting	Surface
9 mm pitches	24
Total number of 18 mm modules	13
Type of rail	DIN
Enclosure material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	IEC 60439-3 IEC 60695-2-1 EN 50102 IEC 60529 EN 60439-3 IEC 23-48
Fire resistance	650 °C (30 s) conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**