

Product data sheet

Characteristics

15211

modular bell transformer - 230 V AC 50 Hz - output 8...12 V - 8 VA



Main

Range	Domae
Product or component type	Transformer
Device short name	TR
Transformer type	Bell transformer

Complementary

[Ue] rated operational voltage	230 V AC 50 Hz
Output voltage	8/12 V :
Output short-circuit protection	Built-in
Rated power in VA	8 VA
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Product weight	240 g
Colour	White
Auxiliary connection terminal	Tunnel type terminals rigid $\leq 2.5 \text{ mm}^2$ Tunnel type terminals flexible $\leq 2.5 \text{ mm}^2$ Tunnel type terminals flexible with ferrule $\leq 2.5 \text{ mm}^2$
Wire stripping length	6 mm top or bottom
Tightening torque	0.5 N.m

Environment

Standards	IEC 61558-2-8 IEC 60529
IP degree of protection	IP40 (in modular enclosure) conforming to IEC 60529 IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

Product Life Status : **Commercialised**