



Commercial status

End of Commercialisation :

△ End of Commercialisation

Main

Range of product	Multi 9
Device short name	TRC 3
Product or component type	Telephone remote control
Number of channels	3
Function available	Access protected via secret code
Type of setting	Can operate in delayed ON/OFF mode
Product compatibility	Compatible with answering machine or fax
Language	English Italian Dutch French Spanish

Complementary

Power consumption in VA	4 VA
Number of outputs	3 output(s) - 1 NO - 230 V
Impulse current [wave 8/20]	10 KA
[Ures] residual voltage	900 V
[Ue] rated operational voltage	230 V AC 50 Hz
Status LED	Indicator light (yellow)on:
9 mm pitches	10
Clamping connection capacity	<= 4 mm ² for flexible cable(s) <= 4 mm ² for rigid cable(s)
Electrical insulation class	Class II
Height	85 Mm
Width	88 Mm
Depth	58 Mm

Environment

Product certifications	CTR21 ART
Ambient air temperature for operation	0...40 °C
IP degree of protection	IP30

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commerc. - Block
-----------------------	-------------------------